




Terminals & Splices > PCB Terminals



Terminal & Splice Type: **Tab**
PCB Terminal Terminal Type: **Tab**
PCB Terminal Mating Tab Width: **4.75 mm [.187 in]**
PCB Terminal Mating Tab Thickness: **.51 mm [.02 in]**
PCB Hole Diameter: **3.68 mm [.145 in]**

Features

Product Type Features

Insertion Force	Normal
FASTON	Yes
PCB Terminal Mounting Style	Stud Mount
Terminates To	Printed Circuit Board

Configuration Features

Stud Hole	Yes
Terminal Angle	Straight

Body Features

PCB Terminal Plating Material	Unplated
-------------------------------	----------

Contact Features

Terminal & Splice Type	Tab
PCB Terminal Terminal Type	Tab
Underplating Material	None
Terminal Size	4.75



PCB Terminal Terminal Orientation	Straight
-----------------------------------	----------

Termination Features

PCB Terminal Termination Method	Screw
---------------------------------	-------

Dimensions

Stud Diameter	3.68 mm[.145 in]
PCB Terminal Mating Tab Width	4.75 mm[.187 in]
PCB Terminal Mating Tab Thickness	.51 mm[.02 in]
PCB Hole Diameter	3.68 mm[.145 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Packaging Features

Packaging Quantity	1000
PCB Terminal Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous



materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 61664-1 FASTON .187 SERIES (4.8 MM) TAB TPBR	 TE Part # 61407-3 FASTON .187 SERIES (4.8 MM) TAB TPBR	 TE Part # 62627-2 FASTON .250 FLAG TEST TAB 032BR	 TE Part # 60920-5 FASTON .187 SERIES (4.8 MM) TAB BR
 TE Part # 60922-5 FASTON .205 (5.21 MM) TAB TPCRS	 TE Part # 62627-3 FASTON .250 FLAG TEST TAB 032BR	 TE Part # 61761-2 FASTON .187 SERIES (4.8 MM) TAB TPBR	 TE Part # 62627-1 FASTON .250 FLAG TEST TAB 032TPCRS
 TE Part # 60921-1 FASTON .205 SERIES (5.21 MM) TAB BR	 TE Part # 60922-1 .205 FAST TEST TAB BR	 TE Part # 62298-3 FASTON .187x.032 (4.75MM) TEST TAB TPBR	 TE Part # 62298-4 FASTON .187x.032 (4.75MM) TEST TAB TPBR

Also in the Series | FASTON 187

Crimp Terminal Housings(40)	Insertion & Extraction Tools(1)	Joints & Splices(1)	PCB Terminals(48)



Quick Disconnects(222)




Splices(1)

Customers Also Bought



TE Part #1-66105-9
TYPE III CONTACTS LP



TE Part #1-640507-0
02P MR II CAP HSG



TE Part #163305-2
MATENLOK PIN SDW



TE Part #1-794608-1
PIN CONT 20-24 15 GOLD STRIP



TE Part #1-350779-9
04P UMNL V0 PLUG HSG BLACK



TE Part #160294
PLASTI-GRIP, RING, 12-10 6MM



TE Part #1-640250-7
3.96mm Wire-to-board housing:
receptacle, with mating alignment, SL
156



TE Part #CQ50423001
RAY-101-4.0(10)



TE Part #160300
PLASTI-GRIP 12-10 RING M10



TE Part #1-480701-0
03P UMNL CAP HSG NATL

Documents

Product Drawings

FASTON .187 SERIES (4.8 MM) TAB BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_60920-1_P.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_60920-1_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_60920-1_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Product Specification](#)

English

Agency Approvals

[UL Report](#)

English