



Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **1.03 – 2.62 mm²**

Quick Disconnect Mating Tab Width: **6.35 mm [.25 in]**

Quick Disconnect Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle
Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp



Barrel Type	Open
-------------	------

Mechanical Attachment

Mating Retention Type	Locking Lance
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	3 – 4.3 mm[.118 – .169 in]
Overall Length	17.1 mm[.673 in]
Receptacle Terminal Stock Thickness	.32 mm[.013 in]
Wire Size	1.03 – 2.62 mm²
Quick Disconnect Mating Tab Width	6.35 mm[.25 in]
Quick Disconnect Mating Tab Thickness	.81 mm[.032 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	100 °C[212 °F]

Packaging Features

Packaging Quantity	10000
Quick Disconnect Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 2-2150014-1
OC-PA-E-FM-110F180F-001-0001

TE Part # 2-2150014-2
OC-PA-E-FA-110F180F-001-0001

TE Part # 2150014-1
OC-AT-E-FM-110F180F-001-0001

TE Part # 2150014-2
OC-AT-E-FA-110F180F-001-0001

TE Part # 626096-2
.250 S FASTIN ON

TE Part # 7-2150014-7
OC-110F180F-CRIMPTOOLINGKIT

Also in the Series | FASTIN-FASTON 250

Crimp Terminal Housings(216)

Insertion & Extraction Tools(2)

PCB Terminals(2)

Quick Disconnects(258)

Customers Also Bought



TE Part #444335-2
FASTON 250 REC 1-5MM2 ELECTRO
TPBR

TE Part #444020-1
TIMER, CONNECTOR HOUSING

TE Part #881778-1
ECONOSEAL, CONNECTOR
HOUSING

TE Part #444442-1
RELAY ADAPTOR 6POSN

TE Part #444308-1
FRAME, FUSE/RELAY B

TE Part #1599962-2
MAXI FUSE BOX WITH JCASE ASSY

TE Part #1599962-3
MAXI FUSE BOX WITH JCASE ASSY

TE Part #1718968-1
ROUND NUT M28x1.5

TE Part #282435-1
MODULAR RELAY HOUSING

Documents

Product Drawings

FF 250 REC 1.0-2.5 MM2 0.32X 19.30 BR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_735222-2_V1_c-735222-2-v1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_735222-2_V1_c-735222-2-v1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_735222-2_V1_c-735222-2-v1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Application Specification

German