



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **4**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Clear**

Features

Product Type Features

Product Type	Terminal Housing
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	4
--	---

Body Features

Crimp Terminal Housing Housing Color	Clear
Crimp Terminal Housing Mating Retention	Without
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Nylon
---	-------

Dimensions

Length	32.5 mm[1.28 in]
Crimp Terminal Housing Centerline	10.79 mm[.425 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	1600
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>






Compatible Parts

 TE Part # 170340-1 FF 250 TAB 20-14AWG BR WITHOUT LATCH	 TE Part # 170341-3 FF 250 TAB 14-12AWG PTBR WITHOUT LATCH	 TE Part # 170349-2 FF 250 TAB 22-20AWG TPBR WITHOUT LATCH	 TE Part # 170340-3 FF 250 TAB 20-14AWG PTBR WITHOUT LATCH
 TE Part # 170341-1 FF 250 TAB 14-12AWG BR WITHOUT LATCH	 TE Part # 170349-1 FF 250 TAB 22-20AWG BR WITHOUT LATCH		

Also in the Series | FASTIN-FASTON 250

 Crimp Terminal Housings(216)	 Insertion & Extraction Tools(2)	 PCB Terminals(2)	 Quick Disconnects(258)
---	--	---	---

Customers Also Bought

 TE Part #1-2040832-4 0.25mm FPC Connectors	 TE Part #1-1734260-5 AMP HPI 1.25MM HEADERS	 TE Part #1-1393239-6 RT114110	 TE Part #1-160301-6 250 FASTON,REC.,10-12 AWG,TPBR
---	---	--	---



TE Part #1-1717834-3
DYNAMIC 2000 REC AND TAB HSG

TE Part #1-969489-1
MQS, CONNECTOR HOUSING

TE Part #1-174355-1
E-J MK-2 CAP HSG 2P NATURAL

TE Part #1-350777-6
02P UMNL V0 PLUG HSG BLUE

TE Part #W4SA
DEUTSCH DT WEDGELOCKS

TE Part #1106402-2
EMV-K.3/4.STO.1.M16.G

Documents

Product Drawings

FF 250 TAB HSG 4P NYLON CLEAR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_737021_B_c-737021-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_737021_B_c-737021-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_737021_B_c-737021-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English

Product Environmental Compliance

Product Compliance



English

Product Compliance

English