



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **4**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Black**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	4
--	---

Body Features

Crimp Terminal Housing Housing Color	Black
Crimp Terminal Housing Mating Retention	Without
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Length	27.33 mm[1.08 in]
Crimp Terminal Housing Centerline	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	6000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>










EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>




Compatible Parts

 TE Part # 180901 FF 250 TAB HSG 4P NYLON NAT	 TE Part # 180908-5 FF 250 TAB HSG 2P NYLON BLACK	 TE Part # 180916-5 FF 250 TAB HSG 1P NYLON BLACK	 TE Part # 925015-1 FF 110 REC HSG 3P NYLON BLACK
 TE Part # 626056-4 FASTIN-ON .110 HOUSING REC PRETO/BLACK	 TE Part # 626057 FASTIN-ON 110 HOUSING TAB NAT 6.6 NYLON	 TE Part # 280072 FF 375 TAB HSG 4P NYLON NAT	 TE Part # 171445-1 FF 250 TAB HSG 14P ASSY CONN
 TE Part # 1-171433-9 FF TAB HSG 6P NYLON BLACK	 TE Part # 1-880298-0 FASTON .250 SERIES (6.3 MM) HOUSING		

Also in the Series | FASTIN-FASTON 110

 Automotive Housings(1)	 Automotive Terminals(4)	 Crimp Terminal Housings(35)	 Insertion & Extraction Tools(3)
---	---	--	--



Quick Disconnects(84)

Customers Also Bought



TE Part #1-1579007-4
EXTRACTION TOOL



TE Part #1-1579007-8
EXTRACTION TOOL



TE Part #1-1437719-2
T01-0540-P05-MALE PLUG
CONNECTOR-CRIMP



TE Part #T2021282201-100
HD-064-FJ 65-128



TE Part #1011-232-0305
DEUTSCH DT BACKSHELLS



TE Part #1-967624-4
TIMER, CONNECTOR HOUSING



TE Part #1-1768046-1
STD SNAP-ON MARKERS



TE Part #1-926539-7
250 FASTON HSG.,REC.,1 POS,BLACK



TE Part #1-928344-2
STD-TIMER GEH 2P

Documents

Product Drawings

FASTIN-ON .110 HOUSING TAB NYLON 6/6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_626057-1_H_c-626057-1-h.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_626057-1_H_c-626057-1-h.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_626057-1_H_c-626057-1-h.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[White Paper: Nylon Discoloration](#)

English

Product Specifications

[Application Specification](#)

English