




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**
Wire Size: **254 – 404 CMA**
Quick Disconnect Mating Tab Width: **2.8 mm, 3.18 mm [.11 in, .125 in]**

Features

Product Type Features

Wire/Cable Type	Regular Wire
Wire Stop	Yes
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Electrical Characteristics

Voltage (Max)	600 V
---------------	-------

Body Features

Insulation Material	Nylon
Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Receptacle
---------------	------------



Terminal & Splice Type	Receptacle
Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Closed

Mechanical Attachment

Mating Retention Type	Dimple
Wire Insulation Support	With

Dimensions

Accepts Wire Insulation Diameter Range	2.54 mm[.1 in]
Overall Length	18.7 mm[.735 in]
Receptacle Terminal Stock Thickness	.41 mm[.016 in]
Wire Size	254 – 404 CMA
Quick Disconnect Mating Tab Width	2.8 mm, 3.18 mm[.11 in][.125 in]
Quick Disconnect Mating Tab Thickness	.51 mm[.02 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

UL Flammability Rating	UL 94V-2
UL Rating	Listed

Packaging Features

Packaging Quantity	3000
Quick Disconnect Packaging Method	Strip/Reel

Other

Barrel Color	Purple
--------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006

Current ECHA Candidate List: JAN 2021 (211)
Candidate List Declared Against: JAN 2021 (211)
Does not contain REACH SVHC

Halogen Content

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 58628-2
PROCIMP DIESET 26-14 ULTRAFast

TE Part # 58628-1
PROCIMP T&D 26-14 ULTRAFast

TE Part # 2-2151693-2
OCEAN-2.0-APPLICATOR-S-136D

TE Part # 2151693-2
OCEAN-2.0-APPLICATOR-S-136D

TE Part # 58052-3
PF UF F-ON SRS 110/125 REC 26-22
DIE SET

TE Part # 7-2151693-2
OCEAN-2.0-APPLICATOR-S-136D

TE Part # 7-2151693-7
OCEAN_2.0_SPARE_PART_KIT-136D

Also in the Series | Ultra-Fast 110



Quick Disconnects(14)

Customers Also Bought



TE Part #1-640251-3
3.96mm Wire-to-board housing:
receptacle, no mating alignment, SL
156



TE Part #1-66359-0
TYPE III CONTACTS STRIP




TE Part #2-1623795-7
Wirewound Resistor: Horizontal Mount



TE Part #2-32959-1
TERMINAL,PG R 16-14 8



TE Part #1658525-2
622-3453LF, PCB IDC, LEAD FREE




TE Part #1-643071-1
11P MTA156 FD-THRU COVER



TE Part #1879450-5
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #CV4186-000
RNF-100-1/4-BK-SP-SH



TE Part #2-520263-4
ULTRA-FAST 250 ASY REC 22-18 TPBR



TE Part #217885-6
CRIMPER, WIRE "F"

Documents

Product Drawings

ULTRA-FAST .110/.125 ASY REC 26-22 TPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_7-520365-2_H.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_7-520365-2_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-520365-2_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ultra-Fast and Ultra Fast Plus](#)

English

Product Specifications

[Application Specification](#)

English

Product Environmental Compliance

[MD_7-520365-2_12122015148_dmtec](#)

English

[MD_7-520365-2_12122015148_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Platform Crimping Die Assembly 58052-3](#)

English

Agency Approvals

[Agency Approval Document](#)

English