




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **6529 – 10382 CMA**

Ring & Spade Stud Size: **#10**

Features

Product Type Features

Shape Description	Anti-Rotational/Grounding
Ring & Spade Stud Size	#10
Ring & Spade Barrel Type	Open Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Ring & Spade Plating Material	Tin
-------------------------------	-----

Contact Features

Contact Base Material	Steel
Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight



Underplating Material	None
-----------------------	------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

	.125 in
Wire Size	6529 – 10382 CMA
Stud Diameter	4.82 mm[.19 in]
Tongue Thickness	.61 mm[.024 in]
Ring & Spade Overall Length	25.14 mm[.99 in]
Barrel Inside Diameter	2.54 mm, 5.25 mm[.1 in][.207 in]
Ring & Spade Wire Insulation Diameter (Max)	5.59 mm[.22 in]
Ring & Spade Wire Insulation Diameter	3.18 – 5.59 mm[.125 – .22 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1800
Ring & Spade Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC



Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 2-2151343-1
OCEAN_2.0_APPLICATOR-S-180F280F



TE Part # 2-2151343-2
OCEAN_2.0_APPLICATOR-S-180F280FA




TE Part # 2151343-1
OCEAN_2.0_APPLICATOR-S-180F280F



TE Part # 2151343-2
OCEAN_2.0_APPLICATOR-S-180F280FA

Customers Also Bought




TE Part #1376391-1
STD Temp Power Key Plug




TE Part #1376394-1
Power Key TPA




TE Part #1-1376391-2
Glow Wire Power Key Plug




TE Part #1-172075-1
3 POS PL 187(4.8 MM) HOUSING NATURAL




TE Part #1-520935-2
PL 250 HOUSING REC RED 6/6 NYLON V2



TE Part #1-520935-1
250 HSG. PL MKII REC. 15.11mm 2P NAT



TE Part #1969657-1
250 FASTON HSG.,FLAG,REC.,1 POS, BLACK



TE Part #1971783-2
POWER TRIPLE LOCK REC CONTACT



Documents

Product Drawings

RING .190 12-10 AWG 0245 TPCRS

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_62613-2_P.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_62613-2_P.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_62613-2_P.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_62613-2_0207201802_dmtec

English

MD_62613-2_0207201802_dmtec

English

Agency Approvals

UL Report

English