




Connectors > Power Connectors > Rectangular Power > Rectangular Power Connectors



Rectangular Power Connector Type: **Housing**

Connector & Housing Type: **Plug**

Connector System: **Wire-to-Wire**

Number of Positions: **9**

Centerline (Pitch): **6.35 mm [.25 in]**

Features

Product Type Features

Rectangular Power Connector Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	9
Number of Rows	3

Electrical Characteristics

Operating Voltage	600 VAC
-------------------	---------

Contact Features

Contact Layout	Matrix
Multiple Contact Types	Without
Contact Retention Within Housing	Without



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Centerline (Pitch)	6.35 mm[.25 in]
Housing Color	White
Housing Material	Nylon

Dimensions

Row-to-Row Spacing	6.35 mm[.25 in]
Width	20.32 mm
Height	20.32 mm
Length	22.99 mm

Usage Conditions

Operating Temperature Range	-55 – 120 °C[-67 – 248 °F]
-----------------------------	----------------------------

Operation/Application

Assembly Integration Feature	Without
Circuit Application	Power & Signal

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
Glow Wire Rating	Standard Part - Not Glow Wire
Agency/Standard Number	E28476
Agency/Standard	CSA, UL
UL Rating	Recognized
CSA File Number	LR7189
VDE Tested	Yes

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Other

--	--



For Use With	Standard Universal MATE-N-LOK Connectors
--------------	--

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 770028-1
09P UMNLI IN-LINE CAP HSG KIT



TE Part # 927231-3
HONHUS UMNL V0 9-P



TE Part # 770040-1
09P UMNL II PLUG REAR 94VO



TE Part # 1586853-1
09P UMNL CAP HSG, GW



TE Part # 927231-5
UNML CAP HSG 9WAY



TE Part # 643254-1
09P UMNL ASSY MOD HSG VO



TE Part # 794538-1
09P UMNL CAP HSG 150C BLK



TE Part # 1969882-1
09P UMNL CAP HSG, P/M, GW V0



TE Part # 2029299-1
9 POS UMNL CAP W/LARGE FLANGE-V0



TE Part # 2029315-1
09P UMNL CAP HSG 150C-RED



TE Part # 2029368-1
09P UMNL-II TW-N-LK-CAP FRONT



TE Part # 2029370-1
09P UMNL-II REAR, TW-N-LK-CAP



TE Part # 2178934-1
CAP, 9 CIRCUIT, UMNL,SPECIAL

Also in the Series | Universal MATE-N-LOK




Circular Power Connectors(2)



Connector Contacts(11)




Insertion & Extraction Tools(4)



Power Contacts(207)



Rectangular Boots & Strain Relief(35)



Rectangular Connector Adapters(7)



Rectangular Connector Housings(2)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Locking(4)



Rectangular Connector Seals(26)



Rectangular Power Connectors(725)

Customers Also Bought



TE Part #786557-7
D-Sub Receptacle Assembly: Vertical,
Action Pin, 1.27mm



TE Part #2-320861-2
PIDG FLANGED SPADE TONGUE
TERMINALS



TE Part #1-794219-0
MINI UNML2 SOK 26-22 AWG AU LF



TE Part #1-794223-0
MINI UMNL2 SCKT 20-16AWG 30AU




TE Part #201350-2
34 PL. PIN HOOD



TE Part #1879450-5
Wirewound Resistor: Mineral, 2.5 Kw



TE Part #2-456406-2
CRIMPER WIRE .090 F



TE Part #2-690471-9
COMB ANVIL



TE Part #1-794222-0
MINI UMNL2 PIN 20-16AWG AU LF



TE Part #2-1393100-6
KBP-11DG-24=KA/KB/KC/KR

Documents

Product Drawings

09P UMNL II PLUG-FRONT 94VO

English

CAD Files

3D PDF

3D

3D PDF

English



Customer View Model

[ENG_CVM_770039-1_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_770039-1_F.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_770039-1_F.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_770039-1_T.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_770039-1_T.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_770039-1_T.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[SOFT_SHELL_PIN_SOCKET_CONNECTORS_STANDARD_DENSITY](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English