




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Receptacle**

Wire Size: **.2 – .51 mm²**

Quick Disconnect Mating Tab Width: **4.75 mm [.187 in]**

Quick Disconnect Mating Tab Thickness: **.5 mm [.02 in]**

Features

Product Type Features

Wire Stop	No
Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Quick Disconnect Insertion Force	Normal
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Receptacle
Terminal & Splice Type	Receptacle



Quick Disconnect Terminal Orientation	Straight
Contact Base Material	Brass
Crimp Type	F-Crimp
Barrel Type	Open

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Accepts Wire Insulation Diameter Range	1.52 – 2.8 mm [.06 – .11 in]
Overall Length	19.18 mm [.755 in]
Receptacle Terminal Stock Thickness	.3 mm [.012 in]
Wire Size	.2 – .51 mm ²
Quick Disconnect Mating Tab Width	4.75 mm [.187 in]
Quick Disconnect Mating Tab Thickness	.5 mm [.02 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]

Packaging Features

Packaging Quantity	12000
Quick Disconnect Packaging Method	Strip/Reel

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 170324-6
POSITIVE LOCK 187 REC 24-20AWG
0.3 PTPBR

TE Part # 2-2836300-2
OCEAN-2.0-APPLICATOR-S-070F140F

TE Part # 2836300-2
OCEAN-2.0-APPLICATOR-S-070F140F

TE Part # 7-2836300-7
OCEAN_2.0_SPARE_PART_KIT-
070F140F

TE Part # 936663-1
PL 187 REC 20-16 AWG 0.3 X 14.0
PTPBR

Also in the Series | Positive Lock 187

Crimp Terminal Housings(87)

Insertion & Extraction Tools(2)

Insulation Boots & Sleeves(9)

Quick Disconnects(56)

Customers Also Bought





TE Part #2-2176057-7
Thick Film Resistor: Current Sense



TE Part #1-2308272-2
CABLE CLAMP FOR SIZE 1-3STD/1-4 QL SHELL



TE Part #1-2308342-3
D-SUB BACKSHELL SIZE 3



TE Part #2098377-1
1.5/2.8 CONNECTOR SYSTEM, HOUSING



TE Part #1718228-2
COVER FOR MQS SOCKET HSG., 12POSN.



TE Part #1-1633930-4
ANVIL, COMBINATION



TE Part #1-528041-3
DIE SET SHIELD CRIMP HVP800 90DEG.35SQMM



TE Part #1803139-3
CRIMPER, INSUL OVERLAP PREM



TE Part #NB19564001
RNF-100-3/16-WH-SP

Documents

Product Drawings

PL 187 RECEPTACLE 24-20 AWG PTPBR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_63196-2_AF.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_63196-2_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_63196-2_AF.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



POS_LOCK_MIL_QRG

English

Product Specifications

Application Specification

English