

MAG-MATE

TE Internal #: 63665-1

MAG-MATE, Magnet Wire Terminals, Tab, Tab, Magnet Wire
Terminal Mating Tab Width 4.75 mm [.187 in]

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Terminal & Splice Type: **Tab**
Magnet Wire Terminal Terminal Type: **Tab**
Magnet Wire Terminal Mating Tab Width: **4.75 mm [.187 in]**
Magnet Wire Terminal Mating Tab Thickness: **.51 mm [.02 in]**
Terminal Height: **7.68 mm [.3 in]**

Features

Product Type Features

Magnet Wire Terminal Wire/Cable Type	Magnet Wire
Sealable	No

Body Features

Cavity Size	Size 2
Magnet Wire Terminal Plating Material	Tin

Contact Features

Terminal & Splice Type	Tab
Magnet Wire Terminal Terminal Type	Tab
Magnet Wire Terminal Terminal Orientation	Straight

Termination Features

Magnet Wire Terminal Termination Method	IDC Standard
---	--------------

Mechanical Attachment

Magnet Wire Terminal Mating Retention Type	Hole
--	------

Dimensions



Magnet Wire Terminal Mating Tab Width	4.75 mm[.187 in]
Magnet Wire Terminal Mating Tab Thickness	.51 mm[.02 in]
Terminal Height	7.68 mm[.3 in]
Aluminum Wire Size	.82 – 1.17 mm
Magnet Wire Size	19 – 17 AWG
Magnet Wire Terminal Material Thickness	.51 mm[.02 in]
Stock Thickness (Magnet Wire Side)	.51 mm[.02 in]
Magnet Wire Terminal Overall Length	15.87 mm[.624 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Identification Marking

Identification Number	28
-----------------------	----

Packaging Features

Packaging Quantity	12000
Magnet Wire Terminal Packaging Method	Reel, Reel/Carton

Other

Comment	After insertion into plastic cavity, tab portion must be bent over 45°-90° or potted in to prevent pullout when mating receptacle is disconnected., Single magnet wire only., Varnish resist coating.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 63273-1
MAG-MATE 187 FAST TAB 020TPBR

TE Part # 1742160-1
TAB,187 FASTON,MAG-MATE

TE Part # 1742159-1
TERMINAL,SPLICE, MAG-MATE

TE Part # 1742159-2
TERM,SPLICE,MAG-MATE

TE Part # 63145-1
MAG-MATE 110 TAB 17-19 020TPBR

TE Part # 1-1579018-9
INSERTION TOOL

TE Part # 63441-1
MAG-MATE 110 F TAB 32-34 TPBR

TE Part # 63511-1
MAG-MATE 187 FAST TAB 020TPBR

TE Part # 63829-1
TERM MAG-MATE 187 FTAB 020TPBR

Also in the Series | **MAG-MATE**



Insertion & Extraction Tools(8)

Magnet Wire Terminals(468)

PCB Terminals(1)

Customers Also Bought

TE Part #1775443-2
AMP HPI 1.5MM HEADERS

TE Part #1-350867-0
01P UMNL PLUG HSG NATL

TE Part #1742800-1
FF 187 TAB 18-14AWG TPBR

TE Part #T1460240121-000
H24B-SDR-BO-PG21

TE Part #1546108-2
EUROSTYLE TB PLUG GREY STKG 2P

TE Part #1217356-1
MAG-MATE TERM 19-17 0157 TPNBR

TE Part #1461492-7
STD OEG PCB OSA Power Relays

TE Part #173724-1
187 PL EX REC. 20-14AWG PTBR

TE Part #1744427-6
EP Header Asy,Shrouded,6 Pos, GW

TE Part #2-1969442-0
EP 2.5 TPA Housing, 20 Pos

Documents

Product Drawings
MAG-MATE 187 FAST TAB 020TPBR

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_63665-1_L.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_63665-1_L.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_63665-1_L.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Magnet Wire Terminals & Splices](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English