




Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Keying



Connector Keying Accessory Type: **Keying Plug**

Features

Product Type Features

Connector Keying Accessory Type	Keying Plug
---------------------------------	-------------

Body Features

Primary Product Material	Nylon
Primary Product Color	Natural

Packaging Features

Packaging Method	Carton
------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability






Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these



limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 86432-1 AMP-0-0086432-1	 TE Part # 85493-4 MOD I RECP LP	 TE Part # 87003-2 MOD I RECP STMPD	 TE Part # 87988-4 04 MODI BDMNT RCPT SR .156CL
 TE Part # 85487-4 MOD I RECP PLTD 30 SEL	 TE Part # 86432-8 MOD I RECP PLTD 30 SEL	 TE Part # 87772-2 MOD I RECP STMPD	 TE Part # 87988-3 03 MODI BDMNT RCPT SR .156CL
 TE Part # 87988-6 06 MODI BDMNT RCPT SR .156CL	 TE Part # 87995-2 02 MODI BDMNT RCPT SR .156CL	 TE Part # 87995-4 04 MODI BDMNT RCPT SR .156CL	 TE Part # 87316-3 MOD I RECP STMPD
 TE Part # 1-87988-9 19 MODI BDMNT RCPT SR .156CL	 TE Part # 86480-2 MOD I RECP LP	 TE Part # 87987-6 06 MODI BDMNT RCPT SR .156CL	 TE Part # 87988-5 05 MODI BDMNT RCPT SR .156CL



TE Part # 1-86477-1
MOD I RECP STMPD/RERELED

TE Part # 1-87987-0
10 MODI BDMNT RCPT SR .156CL

TE Part # 1-87988-0
10 MODI BDMNT RCPT SR .156CL

TE Part # 1-87988-7
17 MODI BDMNT RCPT SR .156CL

Also in the Series | AMPMODU MOD 1

Automotive Terminals(6)

Board-to-Board Connector Contacts
(104)

Board-to-Board Headers &
Receptacles(372)

Board-to-Board Jumpers & Shunts(5)

Insertion & Extraction Tools(1)

PCB Connector Keying(2)

Wire-to-Board Connector Assemblies
& Housings(44)

Wire-to-Board Connector Contacts(2)

Customers Also Bought

TE Part #1-87175-0
04 LOCKING CLIP HSG SR .100CL

TE Part #1-87175-4
06 LOCKING CLIP HSG SR .100CL

TE Part #1-1625890-7
2W SM M/OX 5% 180R

TE Part #11026265-00
Model 44900 Series



TE Part #1883867-1
A600,3, PLUG ASSY 150/60/100/

TE Part #321684
TERMINAL,SOLIS R 16-14 6

TE Part #1-103577-7
MACH APL BAND W/POST 15 DPLX

TE Part #2-1617342-8
HFW1230G01M=M39016/6-112M



Documents

Product Drawings
MODI KEYING PLUG

English

Product Specifications
Application Specification

English

AMPMODU Mod I Receptacle Crimp Contact

English