



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Receptacle**
Housing Type: **Receptacle**
Number of Crimp Terminal Housing Positions: **3**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Natural**

Features

Product Type Features

Product Type	Terminal Housing
Housing Type	Receptacle
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	3
--	---

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	Without
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Receptacle
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Length	18 mm[.708 in]
Crimp Terminal Housing Centerline	5 mm[.196 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Packaging Quantity	6000
--------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 925475-1
FF 110 REC HSG 3P NYLON NAT

TE Part # 925015-1
FF 110 REC HSG 3P NYLON BLACK

TE Part # 925015-3
FF 110 REC HSG 3P NYLON NAT

Also in the Series | FASTIN-FASTON 110

Automotive Housings(1)

Automotive Terminals(4)

Crimp Terminal Housings(35)

Insertion & Extraction Tools(3)

Quick Disconnects(84)

Customers Also Bought

TE Part #150572-2
MINI FASTON 110 REC 20-16 AWG
TPBR

TE Part #1420000-1
MQS, CONNECTOR HOUSING

TE Part #1379675-1
TH/.025 CONNECTOR SYSTEM,
HOUSING

TE Part #1-1419158-7
GET .64 CONNECTOR SYSTEM,
CONNECTOR HSG



TE Part #1-2177909-1
MCON, RECEPTACLE AND TAB

TE Part #1420001-1
MOS VERSCHL.PLATTE

TE Part #1456989-1
2x8 Fem unsealed LP assy Key A

TE Part #1393449-1
V23540A1000Y452=VERSCHL.26P.

TE Part #1563124-1
2. LOCK,10 POS FEM HOUSING

TE Part #CH03496001
QSZH-125-NR2-30MM

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_925015_E.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_925015_E.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_925015_E.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_925015_02282018026_dmtec

English



[MD_925015_02282018026_dmtec](#)

English

[Agency Approvals](#)

[UL Report](#)

English