



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **8**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Connector System	Wire-to-Panel
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	8
--	---

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Body Features

Number of Rows	2
Crimp Terminal Housing Housing Color	Clear
Crimp Terminal Housing Mating Retention	With



Crimp Terminal Housing Mating Alignment	With
Contact Features	
Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight
Mechanical Attachment	
Mating Retention Type	Latch
Crimp Terminal Housing Mounting Style	Panel Mount
Housing Features	
Crimp Terminal Housing Housing Material	Polyamide 6.6
Dimensions	
Height	16.2 mm[.638 in]
Length	40.13 mm[1.58 in]
Width	32.64 mm[1.285 in]
Crimp Terminal Housing Centerline	9.14 mm[.36 in]
Usage Conditions	
Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
Industry Standards	
Crimp Terminal Housing UL Flammability Rating	UL 94V-2
Packaging Features	
Packaging Quantity	100
Crimp Terminal Housing Packaging Method	Carton
Product Compliance	
For compliance documentation, visit the product page on TE.com>	
EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per



homogenous material. Also BFR/CFR/PVC Free


Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 170340-1
FF 250 TAB 20-14AWG BR WITHOUT LATCH



TE Part # 170341-3
FF 250 TAB 14-12AWG PTBR WITHOUT LATCH



TE Part # 170349-2
FF 250 TAB 22-20AWG TPBR WITHOUT LATCH



TE Part # 170340-3
FF 250 TAB 20-14AWG PTBR WITHOUT LATCH



TE Part # 170341-1
FF 250 TAB 14-12AWG BR WITHOUT LATCH




TE Part # 170349-1
FF 250 TAB 22-20AWG BR WITHOUT LATCH



TE Part # 176992-1
250 DBL LOCK CAP IKEI 2P NAT

Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(216)



Insertion & Extraction Tools(2)



PCB Terminals(2)




Quick Disconnects(258)


Customers Also Bought




TE Part #180351-2
FF 250 REC 4-6MM2 PTBR



TE Part #154719-1
250 HSG. PL MKI REC. NAT



TE Part #174922-1
MULTILOCK, CONNECTOR HOUSING




TE Part #1-967644-1
MQS, CONNECTOR HOUSING




TE Part #1241327-1
TIMER, CONNECTOR HOUSING



TE Part #172494-1
MIC MARK-2 PLUG HSG 5P




TE Part #140792-2
SPLICE 5000-12000 0.63MM TPBR



TE Part #1735798-1
HDR ASSY 2mm AMPMODU SMT R/A D



TE Part #EH81736001
ATUM-9/3-X-50MM



TE Part #1703018-1
DIA 1.5MM CONTACT PIN,LP

Documents

Product Drawings

FF 250 8P HOUSING TAB POLYAMID 6.6

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_925341-1_O.3d_igs.zip

English

Customer View Model

ENG_CVM_925341-1_O.3d_stp.zip

English

Customer View Model

ENG_CVM_925341-1_O.2d_dxf.zip

English

3D PDF

English



Customer View Model

[ENG_CVM_CVM_925341-1_C.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_925341-1_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_925341-1_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[White Paper: Nylon Discoloration](#)

English

Product Specifications

[Application Specification](#)

English