



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **2**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing UL Flammability Rating: **UL 94V-0, UL 94V-2**

Features

Product Type Features

Product Type	Terminal Housing
Terminates To	Wire & Cable
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	2
--	---

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	Without
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight



Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Polyamide 6.6
---	---------------

Dimensions

Length	24 mm[.945 in]
Crimp Terminal Housing Centerline	4.5 mm[.177 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

Crimp Terminal Housing UL Flammability Rating	UL 94V-0, UL 94V-2
---	--------------------

Packaging Features

Packaging Quantity	7000
Crimp Terminal Housing Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability








Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part





numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-180908-0 FF 250 TAB HSG 2P NYLON NAT	 TE Part # 174197-1 FASTON .250 SERIES (6.3 MM) HOUSING	 TE Part # 171433-1 FF 250 TAB HSG 6P NYLON NAT	 TE Part # 480116-3 FF 250 TAB HSG 2P NYLON BLACK
 TE Part # 927357-2 FF 110 2P HOUSING PA66 BLACK	 TE Part # 1-171433-4 FF TAB HSG 6P NYLON YELLOW	 TE Part # 1-171433-5 FF TAB HSG 6P NYLON GREEN	 TE Part # 280542 FF 250 TAB HSG 2P NYLON NAT
 TE Part # 1-171433-6 FF TAB HSG 6P NYLON BLUE	 TE Part # 1-171433-9 FF TAB HSG 6P NYLON BLACK		

Also in the Series | FASTIN-FASTON 110

 Automotive Housings(1)	 Automotive Terminals(4)	 Crimp Terminal Housings(35)	 Insertion & Extraction Tools(3)
---	--	--	--



Quick Disconnects(84)

Customers Also Bought




TE Part #1123339-2
TH/.025 CONNECTOR SYSTEM,
HOUSING




TE Part #1473842-2
SIGNAL HEADER



TE Part #1674936-2
TH/.025 CONNECTOR SYSTEM,
RECPT AND TAB



TE Part #1633294-2
ANVIL, WIRE "F"



TE Part #1633005-3
ANVIL, COMBINATION



TE Part #175404-2
HIGH CURRENCY DRAWER ASSY 20P



TE Part #2150347-2
OCEAN_2.0_Applicator-E-100F160F



TE Part #2286546-4
HSD,HDR ASSY,90DEG,COD D



TE Part #CP4912-000
ES2000-NO.2-B9-0-45MM-SH

Documents

Product Drawings

FF 110 2P HOUSING PA66 NATURAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_927357-1_E.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_927357-1_E.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_927357-1_E.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[White Paper: Nylon Discoloration](#)

English

Product Specifications

[Application Specification](#)

English