




Wire Protection & Management > Interconnect Devices > Shielded Contacts



Shielded Contact Product Type: **Contact**
Shielded Contact Wire/Cable Type: **TriAxial**
Shielded Contact Style: **Socket**
Shielded Contact Size: **8**

Features

Product Type Features

Shielded Contact Product Type	Contact
Shielded Contact Wire/Cable Type	TriAxial

Contact Features

Shielded Contact Style	Socket
Shielded Contact Size	8

Termination Features

Termination Method	Solder
--------------------	--------

Usage Conditions

Operating Temperature (Max)	150 °C
-----------------------------	--------

Industry Standards

Government Qualified	No
Military Standard	MIL-C-38999 I, III, IV

Other

Comment	Data Bus Contacts
---------	-------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Pb (37% in Solder) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 750984-004
[10612-24-9](#)

Customers Also Bought



TE Part #121571-000
[TXR40AB00-1610AI](#)



TE Part #106443-000
[TXR40AB00-1408AI](#)




TE Part #132104-2
[TERMINAL RING TONGUE SOLISTRAN](#)




TE Part #120331-000
[RTD-50-M-04](#)



TE Part #131648-3
TERMINAL RING TONGUE PIDG 22 18




TE Part #1506550001
TMS-SCE MILITARY GRADE SLEEVES



TE Part #139515-000
DK-3716-F201-TP



TE Part #1577637-1
TERMINAL RT PIDG PEEK STRATO 14-12 AWG



TE Part #171071-000
DK-3716-E202-TS



TE Part #ZPF000000000019304
FDBA 56-14-19 SN-K 059

Documents

Product Drawings

DK-602-0157-N-2

English

Datasheets & Catalog Pages

Data Bus Components Brochure

English

Product Specifications

Installation Procedure for DK-602-0156 and -0157 Triaxial Contacts

English

Installation Procedure for DK-602-0156 and ?0157 Triaxial Contacts