




Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Shrouds



Connector Mounting Accessory Type:

Shroud

Mating Alignment:

With

Number of Positions:

14

Number of Rows:

1

Number of Columns:

14

Features

Product Type Features

Connector Mounting Accessory Type	Shroud
Sealable	No

Configuration Features

Number of Positions	14
Number of Rows	1
Number of Columns	14

Electrical Characteristics

Termination Resistance	15 mΩ
Insulation Resistance	5000 MΩ
Dielectric Withstanding Voltage (Max)	600 V

Body Features

Shroud Color	Black
Shroud Material	Thermoplastic

Contact Features

CompactPCI	No
------------	----

Mechanical Attachment

Mating Alignment Type	Latched
PCB Mount Retention	Without



Mating Alignment	With
------------------	------

Dimensions

Product Length	49.15 mm[1.93 in]
Product Height	6.35 mm[.25 in]
Product Width	25.15 mm[.99 in]

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	Insert Pin Receptacle Assembly w/Guide Ribs (only) into shroud.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1-103648-3
14 MTE RCPT HSG SR RIB .100CL

TE Part # 1-104503-3
14 MTE PIN HSG SR RIB .100CL

Also in the Series | AMPMODU MTE

Board-to-Board Headers & Receptacles(23)

Insertion & Extraction Tools(2)

PCB Connector Shrouds(40)

Ribbon Connector Accessories(1)

Standard Rectangular Connectors(2)

Wire-to-Board Connector Assemblies & Housings(585)

Wire-to-Board Connector Contacts(32)

Wire-to-Board Headers & Receptacles (740)

Customers Also Bought

TE Part #1375549-1
02 MTE VERT SMT HDR FULL SN-PB

TE Part #2-1747067-4
GRACE INERTIA CONN 2.5 HDR ASSY 4P BLUE

TE Part #1-1879628-5
H4P 510K 1% 100PPM

TE Part #1-2176309-6
RP 1E 0.1W 14R3 0.1% 25PPM 1K RL



TE Part #1776166-5
5P TERMI-BLOK HDR,HIGH TEMP

TE Part #1658462-2
MSB0.80RC-ASY080FL,-,30,-TY

TE Part #218083-000
55A0811-12-6

TE Part #ZPF000000000039500
983-7SE 14-04 SN

TE Part #3-2176067-2
CRG0201 1% 44R2

TE Part #1393102-2
KRP-14AY-120=KA/KB/KC/KR

Documents

Product Drawings

14 MTE PANEL MOUNT SR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-103682-3_N.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-103682-3_N.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-103682-3_N.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

AMPMODU_INTERCONNECTION_SYSTEM_SECTION5_CONT

English

AMP MODU MTE Section of Catalog 1307819

English

AMPMODU MTE INTERCONNECT SYSTEM

English

Product Specifications



Application Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English