880110 ✔ ACTIVE


FASTIN-FASTON | FASTIN-FASTON 250


TE Internal #: 880110

FASTIN-FASTON 250, Crimp Terminal Housings, Receptacle, Receptacle, 4 Position, Straight, Natural Crimp Terminal Housing Housing Color, Nylon

View on TE.com >

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings




Terminal & Splice Type: **Receptacle**

Housing Type: **Receptacle**

Number of Crimp Terminal Housing Positions: **4**

Crimp Terminal Housing Terminal Orientation: **Straight**

Crimp Terminal Housing Housing Color: **Natural**

Features

Product Type Features

Product Type	Terminal Housing
Housing Type	Receptacle
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	4

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	Without
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Receptacle
Crimp Terminal Housing Terminal Orientation	Straight

Mechanical Attachment

Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)

Housing Features

Crimp Terminal Housing Housing Material	Nylon

Dimensions

Length	23.1 mm[.91 in]
Crimp Terminal Housing Centerline	10.8 mm[.425 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]

Packaging Features

Packaging Quantity	3000
Crimp Terminal Housing Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts



TE Part # 170258-2
FF 250 REC 14-12AWG TPBR REREELING



TE Part # 170258-1
FF 250 REC 14-12AWG BR REREELING



TE Part # 880097-1
2 WAY FASTIN ON HSG



TE Part # 880103-1
5 WAY FASTIN ON HSG



TE Part # 880192-1
5W FASTIN-ON REC. H

Also in the Series | FASTIN-FASTON 250




Crimp Terminal Housings(216)



Insertion & Extraction Tools(2)



PCB Terminals(2)




Quick Disconnects(258)


Customers Also Bought




TE Part #35773
TERMINAL,SOLIS R 12-10 5/16




TE Part #280314
FF 250 REC HSG 6P NYLON CLEAR




TE Part #926097-1
FF 250 TAB HSG 3P NYLON NAT



TE Part #180908-5
FF 250 TAB HSG 2P NYLON BLACK




TE Part #180907-5
FF 250 REC HSG 2P NYLON BLACK




TE Part #1-735075-0
250 FASTON INS POST,REC.,1 POS




TE Part #154719-1
250 HSG. PL MKI REC. NAT



TE Part #171706-1
FASTON 250 INS POD NYLON NAT



TE Part #280099
FF 250 TAB HSG 8P NYLON CLEAR



TE Part #170234-2
PL 250 REC 12-10 AWG 0.406 X 42.3

Documents

CAD Files

Customer View Model

ENG_CVM_880110_F.3d_igs.zip

English

Customer View Model

ENG_CVM_880110_F.3d_stp.zip

English

Customer View Model

ENG_CVM_880110_F.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.