




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**
Connector & Housing Type: **Plug**
Connector System: **Wire-to-Wire**
Number of Positions: **16**
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Plug
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	16
Number of Rows	2

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Type	Socket
Contact Current Rating (Max)	7.5 A



Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Nylon - GF
Centerline (Pitch)	2.5 mm[.098 in]
Housing Color	White

Dimensions

Connector Length	21.04 mm[.828 in]
Connector Height	8.3 mm[.326 in]
Connector Width	12.32 mm[.485 in]
Wire Size	.13 – .33 mm ²
Row-to-Row Spacing	2.5 mm[.09 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1500
Packaging Method	Bag

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-1969540-8
HOUSING, PLUG, 8P, DUAL ROW, EP2.5



TE Part # 2-1969540-0
HOUSING, PLUG, 20P,DUAL ROW, EP2.5



TE Part # 1-1969540-2
HOUSING, PLUG, 12P, DUAL ROW, EP2.5



TE Part # 1-1969540-0
HOUSING, PLUG, 10P,DUAL ROW, EP2.5



TE Part # 1-2323743-2
HOUSING, PLUG, GWT, 12P, DUAL ROW, EP2.5



TE Part # 1-2323743-6
HOUSING, PLUG, GWT, 16P, DUAL ROW, EP2.5



TE Part # 1-2324579-6
HOUSING, PLUG, 16P, DUAL ROW, EP2.5




TE Part # 1-1969540-4
HOUSING, PLUG, 14P,DUAL ROW, EP2.5



TE Part # 1-1969540-8
HOUSING, PLUG, 18P,DUAL ROW,
EP2.5



TE Part # 1-1969567-6
HOUSING, PLUG, GWT, DUAL ROW,
EP2.5



TE Part # 4-1969540-0
HOUSING, PLUG, 40P,DUAL ROW,
EP2.5

Also in the Series | Economy Power 2.5



Insertion & Extraction Tools(1)



PCB Latches, Locks & Retainers(49)




Rectangular Power Connectors(43)



Wire-to-Board Connector Assemblies
& Housings(216)



Wire-to-Board Connector Contacts(6)




Wire-to-Board Headers & Receptacles
(209)

Customers Also Bought



TE Part #T4140412021-000
M12 Panel Mount PCB



TE Part #166309-3
MOD-5 REC.CONTACT



TE Part #1-1969582-0
ASSY, HDR, VERT, NO-BOSS, DUAL
ROW,EP2.5



TE Part #1-1969540-2
HOUSING, PLUG, 12P, DUAL ROW,
EP2.5



TE Part #1-1969541-2
RETAINER, TPA, DUAL ROW, EP2.5



TE Part #1601009-4
PC TAB STANDARD SIAMEZE



TE Part #1-1969541-8
RETAINER, TPA, DUAL ROW, EP2.5



TE Part #1-1969541-6
RETAINER, TPA, DUAL ROW, EP2.5



TE Part #1-1969540-4
HOUSING, PLUG, 14P,DUAL ROW,
EP2.5



TE Part #1-1969540-8
HOUSING, PLUG, 18P,DUAL ROW,
EP2.5

Documents

Product Drawings

HOUSING, PLUG, 16P,DUAL ROW, EP2.5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-1969540-6_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1969540-6_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1969540-6_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773461-6_EP2.5_Connector_Series

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_1-1969540-6_10312018311_dmtec

English

MD_1-1969540-6_10312018311_dmtec

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

1-1969540-6

Economy Power 2.5, Housing, Plug, Wire-to-Wire, 16 Position, 2.5mm [.098in]
Centerline, Crimp, 2 Row, Row-to-Row Spacing .09 in [2.5 mm]



VDE Certificate

English