




MTA | SL-156

TE Internal #: 1-2132189-2

SL-156, Housing, Receptacle, Wire-to-Board, 12 Position, 3.96mm [.156in] Centerline, Crimp, 1 Row, Natural Housing Color, Mating Retention

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings > 3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **12**

Centerline (Pitch): **3.96 mm [.156 in]**

[All 3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156 \(124\)](#)

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	12
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

--	--



Contact Layout	Inline
Contact Retention Within Housing	Without
Contact Type	Socket
Contact Base Material	Phosphor Bronze
Contact Current Rating (Max)	6.5 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Strain Relief	Without
PCB Mount Alignment	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Locking Ramp
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon - GF
Centerline (Pitch)	3.96 mm[.156 in]
Housing Color	Natural

Dimensions

Connector Length	47.52 mm[1.871 in]
Wire Size	.205 – .8 mm²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
UL File Number	E28476
UL Rating	Listed
Agency/Standard	CSA, UL



CSA File Number

LR 7189

Packaging Features

Packaging Quantity	500
Packaging Method	Bag

Other

Comment	Unit Accepts 1.14[.045] Square or Round Post, Accepts Keying Plug 640254-1and 640255-1
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



 TE Part # CAT-103156-WBHSM 3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156	 TE Part # 1-640384-2 12P MTA156 HDR ASSY STR RND SN	 TE Part # 4-641210-2 12P MTA156 HDR FLRA FB 30AU LF	 TE Part # 4-641435-2 12P MTA156 CONN ASSY ORNG
 TE Part # 1-640385-2 12P MTA156 HDR ASSY SQ R/A	 TE Part # 1-640389-2 12P MTA156 HDR ASSY SQ R/A F/L	 TE Part # 1-640388-2 12P MTA156 HDR ASSY RN STR F/L	 TE Part # 1-640445-2 12P MTA156 HDR ASSY FL/STR SN
 TE Part # 1-640383-2 12P MTA156 HDR ASSY STR SQ SN	 TE Part # 1-643067-2 12P MTA156 MOLDED COVER	 TE Part # 1-643071-2 12P MTA156 FD-THRU COVER	 TE Part # 4-641208-2 12P MTA156 HDR ASSY FL ST LF
 TE Part # 4-644615-2 12P MTA156 POL HDR ASSY LF	 TE Part # 1-640387-2 12P MTA156 HDR ASSY SQ R/A	 TE Part # 1-640551-2 12P MTA156 COVER	 TE Part # 1-644752-2 12P MTA156 HDR ASSY SQ STR F/L
 TE Part # 640254-1 KEYING PLUG .045 SQ PST CONN	 TE Part # 3-647123-2 12P MTA156 SHRD HDR ASSY SQ SN	 TE Part # 1-644753-2 12P MTA156 HDR ASSY RN STR F/L	 TE Part # 2-2132074-0 20Pos SL156 Contact Retainer


Also in the Series | **SL-156**



Insertion & Extraction Tools(1)



PCB Connector Keying(2)



PCB Latches, Locks & Retainers(1)



Rectangular Connector Housings(12)



Rectangular Connector Keying Plugs(1)




Wire-to-Board Connector Assemblies & Housings(157)



Wire-to-Board Connector Contacts(24)

Customers Also Bought



TE Part #1775099-8
ATX PWR CONN 1 BDLK 12 POS



TE Part #2331374-1
DET SW3.50X2.8X1.5 JB VERT. NO AG RL



TE Part #2337234-2
TACT MICRO JB 4.6X4.4X0.55 P3.5 160GF



TE Part #2-1445087-8
MICRO MNL HDR ASSY S/ROW AU LF



TE Part #2213774-4
AV16 SPM 0.4VA FIX RING LED RED 24V



TE Part #8-2176309-5
RP 1E 0.1W 75R 0.1% 25PPM 1K RL



TE Part #2132189-8
3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156



TE Part #1-644752-2
12P MTA156 HDR ASSY SQ STR F/L



TE Part #1408337-1
QMA RIGHT ANGLE PWB JACK



TE Part #2267088-4
RAD1R102M6QES

Documents



Product Drawings

12P SL156 HSG W/LCK RMP, TABS & RTNR

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-2132189-2_C_c-1-2132189-2-c.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-2132189-2_C_c-1-2132189-2-c.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-2132189-2_C_c-1-2132189-2-c.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773461-7_SL-156_CONNECTOR_TPA_DEVICE

English

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

Agency Approval Document

English