



Rail D-Sub Backshells

TE Internal #: 1-2308273-1

Rail D-Sub Backshells, D-Sub Backshells & Clamps, Quick Lock Pins, Shielded, Wire & Cable, Operating Temperature Range -40 – 90 °C [-40 – 194 °F]

[View on TE.com >](#)

Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Backshells & Clamps > QLPIN FOR D-SUB W/ FIXED FEMALE SCREWL.



D-Shaped Connector Accessories: Quick Lock Pins

Shielded: Yes

Connector & Contact Terminates To: Wire & Cable

Operating Temperature Range: -40 – 90 °C [-40 – 194 °F]

All QLPIN FOR D-SUB W/ FIXED FEMALE SCREWL. (2)

Features

Product Type Features

Clam Shell Length	Standard
Grommets	Without
Slide Latch	Without
Product Type	Backshell/Cable Clamp
D-Shaped Connector Accessories	Quick Lock Pins
Connector & Contact Terminates To	Wire & Cable

Mechanical Attachment

Screw & Hole Thread Size	M3
--------------------------	----

Usage Conditions

Operating Temperature Range	-40 – 90 °C[-40 – 194 °F]
-----------------------------	---------------------------

Operation/Application

Shielded	Yes
----------	-----

Packaging Features

Packaging Quantity	500
Packaging Method	Box



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2308319-1
FULL METAL HOODS SIZE 1 (1)



TE Part # 1-2308321-1
FULL METAL HOODS SIZE 2, (1)



TE Part # 1-2308327-1
FULL METAL HOODS SIZE 3 (1)



TE Part # 1-2308330-1
FULL METAL HOODS SIZE 4 (1)



TE Part # 1-2308338-1
QL-FULL METAL HOODS SIZE 5 (1 CABLE CLP)

Also in the Series | Rail D-Sub Backshells

Crimp D-Sub Connectors(10)

D-Sub Backshells & Clamps(143)

D-Sub Connector Contacts(5)

Customers Also Bought

TE Part #1-2176416-5
9W STD M/OX 5% 200R

TE Part #2-2176416-7
9W STD M/OX 5% 620R

TE Part #1-1879451-3
Wirewound Resistor: Mineral, 2.5 Kw

TE Part #814609-000
214A342-3-0

TE Part #ZPF000000000015177
DMC-M 01-08 SN

TE Part #9094114002
LSTT-9.5-4-SP

TE Part #2217484-2
KIT, BTLI, HEAVY HEAD

TE Part #2362768-1
MATENET,PIGTAIL,1 GBPS UTP

TE Part #1-2176361-9
RQ 0402 7K15 0.1% 10PPM 1K RL



Documents

Product Drawings

QL-SET VAR A W/STP MO FOR COMBLOCK M3THD

English

Datasheets & Catalog Pages

Rail D-Sub Backshells Flyer

English