


1376473-3 x OBSOLETE

### AMP Signal Double Lock

TE Internal #: 1376473-3

TE Internal Description: 2.5 SMC H-HDR 3POS WHITE (LP)

[View on TE.com >](#)



### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Also in the Series | [AMP Signal Double Lock](#)




Connector Contacts(9)



Insertion & Extraction Tools(1)



PCB Connector Seals(1)



PCB Latches, Locks & Retainers(17)



Rectangular Caps & Covers(1)



Rectangular Connector Housings(23)



Rectangular Connector Locking(2)



Rectangular Connector Seals(10)



Rectangular Power Connectors(3)




Standard Rectangular Connectors(1)



Wire-to-Board Connector Assemblies & Housings(74)



Wire-to-Board Connector Contacts(6)



Wire-to-Board Headers & Receptacles (157)


## Customers Also Bought



TE Part #3-1879453-1  
Wirewound Resistor: Mineral, 2.5 Kw




TE Part #6-1879352-9  
RR02 5% 220R AMMO




TE Part #9-2176397-4  
3502 7K5 1%



TE Part #4-1879352-8  
RR02 5% 30R AMMO



TE Part #1986371-3  
Str Plug, 3.5mm, Green, LH, 3



TE Part #6-102619-5  
34 MODII HDR DRST SHRD .100CL



TE Part #2-1623795-3  
Wirewound Resistor: Horizontal Mount



TE Part #YDTS24T21-35SNV001  
Jam Nut: D38999, 21-35 Insert



TE Part #42021  
FASTON 250 (6.3MM) REC 16-12 AWG  
TPBR



TE Part #D369-R99-CS0  
369 9 WAY REC, NO CONTACTS, SKT

## Documents

### Product Drawings

#### 2.5 SMC H-HDR 3POS WHITE (LP)

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1376473-3\\_A\\_c-1376473-3-a.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1376473-3\\_A\\_c-1376473-3-a.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_1376473-3\\_A\\_c-1376473-3-a.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

#### Application Specification

English