



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal & Splice Type: **Tab**
Housing Type: **Tab Housing**
Number of Crimp Terminal Housing Positions: **16**
Crimp Terminal Housing Terminal Orientation: **Straight**
Crimp Terminal Housing Housing Color: **Natural**

Features

Product Type Features

Product Type	Terminal Housing
Housing Type	Tab Housing
Sealable	No
Insulated	No

Configuration Features

Number of Crimp Terminal Housing Positions	16
--	----

Body Features

Crimp Terminal Housing Housing Color	Natural
Crimp Terminal Housing Mating Retention	With
Crimp Terminal Housing Mating Alignment	With

Contact Features

Terminal & Splice Type	Tab
Crimp Terminal Housing Terminal Orientation	Straight

Mechanical Attachment



Crimp Terminal Housing Mounting Style	Cable Mount (Free-Hanging)
---------------------------------------	----------------------------

Housing Features

Crimp Terminal Housing Housing Material	Polyamide
---	-----------

Dimensions

Width	24.4 mm
Length	63 mm[2.48 in]
Crimp Terminal Housing Centerline	6.5 mm[.255 in]

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Packaging Features

Crimp Terminal Housing Packaging Method	Carton
---	--------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2018 (181) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability










Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the





product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

 TE Part # 180901 FF 250 TAB HSG 4P NYLON NAT	 TE Part # 180908 FF 250 TAB HSG 2P NYLON NAT	 TE Part # 180924 FF 250 TAB HSG 2P NYLON NAT	 TE Part # 1-180908-0 FF 250 TAB HSG 2P NYLON NAT
 TE Part # 180906 FF 250 TAB HSG 6P NYLON NAT	 TE Part # 880298-1 2 WAY FF 250 HOUSING TAB NATURAL	 TE Part # 280924 FF 250 & 375 TAB HSG 2P NYLON NAT	 TE Part # 1-626065-2 FF 110 2P HOUSING TAB NATURAL PA6.6 V-0
 TE Part # 4-180924-0 FF 250 TAB HSG 2P NYLON NAT	 TE Part # 1-480251-0 FF 187 TAB HSG 3P NYLON NAT		

Customers Also Bought

 TE Part #2-1241961-8 STD TIM HOUSING MKII 3POS	 TE Part #1241964-7 STD TIM HOUSING 7P	 TE Part #1-1241961-8 STD TIM HOUSING MKII 3POS	 TE Part #2-520102-2 ULTRA-FAST 250 ASSEMBLY TAB 22-18 AWG BR
---	---	---	---



Documents

Product Drawings

FF 203 TAB HSG 16P NYLON NAT

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_927670-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_927670-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_927670-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

FASTIN-FASTON CONN. .110 INCH, .187 INCH, .250 INCH, .375 INCH SRS.

English

Product Specification

English

Product Environmental Compliance

TE Material Declaration

English

