




Terminals & Splices > Quick Disconnects



Terminal & Splice Type: **Tab**
Wire Size: **1021 – 2048 CMA**
Quick Disconnect Mating Tab Width: **2.8 mm [.11 in]**

Features

Product Type Features

Wire/Cable Type	Regular Wire
Terminates To	Wire & Cable
Sealable	No
Insulated	No

Configuration Features

Connection Capacity	Single
---------------------	--------

Body Features

Fully Insulated	No
Quick Disconnect Plating Material	Tin

Contact Features

Terminal Type	Tab
Terminal & Splice Type	Tab
Quick Disconnect Terminal Orientation	Straight
Contact Base Material	CuZn30
Crimp Type	F-Crimp
Barrel Type	Open



Mechanical Attachment

Mating Retention Type	Locking Lance
Locking Lance Height	1.2 mm[.047 in]

Dimensions

Accepts Wire Insulation Diameter Range	1.6 – 2.2 mm[.063 – .087 in]
Overall Length	22.5 mm[.886 in]
Wire Size	1021 – 2048 CMA
Quick Disconnect Mating Tab Width	2.8 mm[.11 in]
Quick Disconnect Mating Tab Thickness	.79 mm[.031 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-40 – 130 °C[-40 – 266 °F]

Packaging Features

Packaging Quantity	4000
Quick Disconnect Packaging Method	Reel

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part




numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 2305570-1 TERMINAL CUTTER, SIDE FEED	 TE Part # 2-2151155-1 OCEAN_2.0_Applicator-S-080F120F	 TE Part # 2-2151155-2 OCEAN_2.0_Applicator-S-080F120FA	 TE Part # 2151155-1 OCEAN_2.0_Applicator-S-080F120F
 TE Part # 2151155-2 OCEAN_2.0_Applicator-S-080F120FA	 TE Part # 7-2151155-1 OCEAN_2.0_Applicator-S-080F120F	 TE Part # 7-2151155-2 OCEAN_2.0_Applicator-S-080F120FA	 KIT REPRESENTATION ONLY TE Part # 7-2151155-7 OCEAN_2.0_SPARE_PART_KIT-080F120F

Also in the Series | FASTIN-FASTON 110

 Automotive Housings(1)	 Automotive Terminals(4)	 Crimp Terminal Housings(35)	 Insertion & Extraction Tools(3)
 Quick Disconnects(84)			

Customers Also Bought



TE Part #106455-3
FF 110 PLUG HSG 8P.

TE Part #160450-2
FF 250 TAB 18-14AWG TPPB

TE Part #1-967630-5
TIMER, CONNECTOR HOUSING

TE Part #1-968968-3
CIRCULAR DIN HOUSINGS

TE Part #1-967590-1
AMP MCP, RECEPTACLE AND TAB

TE Part #1318774-1
TH/.025 CONNECTOR SYSTEM, HOUSING

TE Part #106455-4
FF 110 PLUG HSG 8P.

TE Part #160366-2
FF 110 SR. REC 22-20AWG TPBR

TE Part #NB07744001
HTAT-24/6-0-SP

Documents

Product Drawings

FF 110 TAB 0.5-1 MM2 PTP CUSN30

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_927892-1_S.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_927892-1_S.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_927892-1_S.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.