



Connectors > RF Coax Connectors > RF Coax Accessories > Ferrules



Compatible With RF Cable Type: 21-598, RG 174, RG 179A, RG 187, RG 188

Ferrule Material: **Copper Alloy**

Ferrule Plating Material: **Tin**

Accepts Wire Insulation Diameter Range: 3.05 mm [.12 in]

Features

Product Type Features

Connector Type	Coaxial Contacts
Compatible With RF Cable Type	21-598, RG 174, RG 179A, RG 187, RG 188

Body Features

Body Plating Material	Tin
-----------------------	-----

Contact Features

Ferrule Material	Copper Alloy
Ferrule Plating Material	Tin

Dimensions

Accepts Wire Insulation Diameter Range	3.05 mm[.12 in]
--	-----------------

Packaging Features

Packaging Method	Package
------------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
------------------------------	-----------



EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 201142-2
RETENTION SPRING,PLTD




TE Part # 476408
SAHT S E COAXIAL F BNC RG U 174-188 ASSY

Customers Also Bought



TE Part #1658640-2
D-Sub Crimp Recpt Signal 50 Posn, Socket Size 20, Shell Size 5




TE Part #200277-2
FEMALE BLOCK 50 PL



TE Part #1757824-8
AMPLIMITE,ASY,RCPT,STD,90,ZN,2,CONT



TE Part #200867-1
SERIES "M" JACKSCREW FEM. ASSY



Documents

Product Drawings

FERRULE, LEAD FREE PLATING

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9-328666-1_BH.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9-328666-1_BH.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9-328666-1_BH.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

Agency Approval Document

English

Agency Approval Document

English