




Terminals & Splices > Ring Terminals & Spade Terminals



Wire Size: 3 – 6 mm²

Stud Diameter: 8.4 mm [.331 in]

Ring & Spade Barrel Type: Closed Barrel

Ring & Spade Terminal Orientation: Straight

Features

Product Type Features

Shape Description	RING-008
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	Yes
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Insulation Sleeve Color	Yellow
Weight per Piece	2.404 g[.0847 oz]
Ring & Spade Plating Material	Tin

Contact Features

Ring & Spade Terminal Orientation	Straight
-----------------------------------	----------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------



Dimensions

Wire Size	3 – 6 mm²
Stud Diameter	8.4 mm[.331 in]
Ring & Spade Overall Length	45 mm[1.77 in]
Barrel Inside Diameter	6.5 mm[.256 in]

Usage Conditions

Insulation Requirement	Partially Insulated
Operating Temperature Range	-55 – 125 °C

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	500
Ring & Spade Packaging Method	Package

Other

Comment	Crimp Termination
---------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent



chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CJ2087-000
HL2010E-KIT-120V

Customers Also Bought

TE Part #1-747943-5
IDC D-Sub: Receptacle Kit, Wire to Wire, Signal, 2.74 mm

TE Part #108961-000
D-406-0003

TE Part #1011-273-0205
DEUTSCH DT BACKSHELLS

TE Part #1-967622-6
TIMER, CONNECTOR HOUSING

TE Part #0937690001
TMS-SCE MILITARY GRADE SLEEVES

TE Part #952651-000
B-106-1501

TE Part #160450-3
FF 250 TAB 18-14AWG PB SILVER PL

TE Part #1231953001
VG-95218-T028-D001CK3100

TE Part #142458-000
TTMS-38.1-9

TE Part #086523-000
KTKK-1120

Documents



Product Drawings

B-106-1803

English

Datasheets & Catalog Pages

1654025_Sec8_B-106

English

Raychem Electrical Interconnect Products

English

Product Specifications

Installation Procedure for Duraseal Splices and Terminals

English