



Wire Protection & Management > Interconnect Devices > SolderSleeve Shield Terminators



SolderSleeve Shield Terminator Operating Temperature (Max): 125 °C

Pre-Installed Lead: No

Features

Configuration Features

Pre-Installed Lead	No
--------------------	----

Usage Conditions

SolderSleeve Shield Terminator Operating Temperature (Max)	125 °C
--	--------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




TE Part # CJ2087-000
[HL2010E-KIT-120V](#)

Customers Also Bought



TE Part #54771-1
[PIDG RING TONGUE TERMINALS](#)



TE Part #485893-8
[010 HOUSING FFC PIN 100CL SR](#)



TE Part #6609012-6
[CORCOM H SERIES SINGLE PHASE FILTERS](#)




TE Part #1-172160-9
[MINI UNIVERSAL M-N-L CAP 6P](#)



TE Part #E77815-000
[B-155-1503](#)



TE Part #1-172162-2
[12 POS TR MINI UNIV](#)



TE Part #5-104895-1
[10 50/50 GRID RA HDR W/LTCH LF](#)



TE Part #1419108-8
[RT314005F](#)



TE Part #1-770834-1
[MINI UMNL SOK PHBRZ AU LF](#)

Documents

Product Drawings
[B-155-9101](#)
English



Datasheets & Catalog Pages

Raychem Electrical Interconnect Products

English

Product Specifications

SolderSleeve One-Step Wire and Cable Terminators Installation Procedures for CWT and B-155 Products

English