



Connectors > Connector Backshells & Adapters > Ruggedized Backshells & Adapters



Connector General Specification Number: MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W

Backshell Material: Aluminum

Adapter Plating Material: Zinc Nickel (ASTM B841)

Cable Diameter Range: 7.9 – 12.7 mm [.313 – .5 in]

Adapter Angle: Straight

Features

Product Type Features

Termination Device Included	TR10AI
Pluggable I/O Accessory Type	Tinel-Lock Adapter
Adapter Angle	Straight
Termination Device Type	Side-Entry Tinel-Lock Ring, Tinel-Lock Adapter, Tinel-Lock Ring
Connector Shell Size	13, C

Body Features

Color	Black
Backshell Material	Aluminum
Adapter Plating Material	Zinc Nickel (ASTM B841)
TE Adapter Code	40
Adapter Entry Size	10

Termination Features

Overbraid Termination	Tinel-Lock Ring
-----------------------	-----------------

Dimensions

Cable Entry Diameter	.2 – 15.9 mm[.01 – .63 in]
Cable Diameter Range	7.9 – 12.7 mm[.313 – .5 in]

Usage Conditions



Salt Spray Resistance	500 Hr
Operating Temperature Range	-65 – 175 °C[-85 – 347 °F]

Industry Standards

Connector Detail Specification Number	D38999/20, D38999/24, D38999/26, D38999/40, D38999/42, D38999/46, D38999/47
---------------------------------------	---

Other

Connector General Specification Number	MIL-DTL-38999 Series III/Class C,F,K,W, MIL-DTL-38999 Series IV/Class C,F,W, MIL-DTL-38999 Series IV/Class C,W, MIL-DTL-38999 Series IV/Class F,W
--	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (.3% in BACKSHELL AND NUT) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts




TE Part # 173643-000
RH-3960-1-TINEL-KIT-120V

Customers Also Bought



TE Part #146893-1
Free Height Receptacle Conn: Board-Board, Vertical, 64, 1mm



TE Part #3-1630024-2
Power Resistors: Aluminum Housed, HSA



TE Part #1676267-1
RN 0805 255R 0.1% 10PPM CUT LENGTH



TE Part #1676288-1
RN 0805 2K37 0.1% 10PPM CUT LE




TE Part #YDTS26Z25-24SAV001
D38999: Straight Plug, 25-24 Insert



TE Part #6-338309-2
D-Sub Plug Assembly: Standard, Vertical, Shell Size 1, 2.74mm



TE Part #905802-000
ST63-2-55-22-90



TE Part #445190-000
0024A0311-0



TE Part #1676236-1
RN 0805 1K58 0.1% 10PPM CUT LENGTH



TE Part #A96559-000
TXR40AU00-2016BI

Documents

Product Drawings
STXR40AZ00-1210AI

English

CAD Files
3D PDF
3D



Customer View Model

[ENG_CVM_CVM_CH5547-000_A.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_CH5547-000_A.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_CH5547-000_A.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[5-1654025-5_sec6_Adapters](#)

English

Circular Backshells

English

Product Specifications

[General Information Package for Tinel-Lock Adapters](#)

English

[Braid termination using a Tinel Lock Ring installed using a resistance heater.](#)

English

[PERFORMANCE SPECIFICATION Tinel-Lock Rings, Heat Recoverable for Braid Termination](#)

English

[ASSEMBLY GUIDE for Tinel -Lock Rings, Heat Recoverable for Braid Temination](#)

English

[Braid termination using a Tinel Lock Ring installed using a resistance heater.](#)

French

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English