


Economy Power 2.5

TE Internal #: 1969730-8
Economy Power 2.5, PCB Mount Header, Vertical, Wire-to-Board, 8
Position, 2.5mm [.098in] Centerline, 1 Row, Tin, Natural Housing
Color, Fully Shrouded

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Wire-to-Board**
Number of Positions: **8**
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	8
Number of Rows	1

Contact Features

Contact Retention Within Housing	Without
Mating Pin Diameter	.6 mm[.024 in]
Contact Underplating Material	Nickel
Contact Mating Area Plating Material	Tin



Contact Mating Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	2 – 5 µm[80 – 200 µin]
Contact Type	Pin
Contact Current Rating (Max)	4.2 A

Termination Features

Round Termination Post & Tail Diameter	.6 mm[.024 in]
Termination Method to Wire & Cable	Crimp
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Locating Posts
PCB Mount Retention Type	Boardlock
PCB Mount Alignment	With
Mating Retention	With
PCB Mount Retention	With
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
Housing Color	Natural
Housing Material	PBT GF

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag & Box
------------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1969730-6 EP2.5 SHROUDED HDR ASSY 6P VERTICAL	 TE Part # 1969730-2 EP2.5 SHROUDED HDR ASSY 2P VERTICAL	 TE Part # 1969730-3 EP2.5 SHROUDED HDR ASSY 3P VERTICAL	 TE Part # 1969730-4 EP2.5 SHROUDED HDR ASSY 4P VERTICAL
 TE Part # 1969730-5 EP2.5 SHROUDED HDR ASSY 5P VERTICAL	 TE Part # 1969730-7 EP2.5 SHROUDED HDR ASSY 7P VERTICAL	 TE Part # 1969730-9 EP2.5 SHROUDED HDR ASSY 9P VERTICAL	 TE Part # 1969541-8 RETAINER, TPA, DUAL ROW, EP2.5



TE Part # 1-1969730-4
EP2.5 SHROUDED HDR ASSY 14P
VERTICAL

TE Part # 2132230-8
EP2.5 Shrouded HDR ASSY 8P VER

TE Part # 1-1969730-1
EP2.5 SHROUDED HDR ASSY 11P
VERTICAL

Also in the Series | Economy Power 2.5

Insertion & Extraction Tools(1)

PCB Latches, Locks & Retainers(49)

Rectangular Power Connectors(43)

Wire-to-Board Connector Assemblies
& Housings(216)

Wire-to-Board Connector Contacts(6)

Wire-to-Board Headers & Receptacles
(209)

Customers Also Bought

TE Part #1-1969688-3
POWER TRIPLE LOCK HIGH TEMP
HEADER

TE Part #1376383-1
Glow Wire Power Key Header

TE Part #1217057-1
187 FASTON,PCB TAB,TPBR

TE Part #647676-3
3.96 EP HDR ASSY 3P R/A

TE Part #1-1376385-2
5mm B-T-W Conn. 6P HDR ASSEMBL

TE Part #1-1376384-5
5mm B-T-W Conn. 4P HDR ASSEMBLY
(GWT)

TE Part #1-282004-2
AMP MONO-SHAPE TAB CONN 4P. G

TE Part #1217041-1
TAB, POKE IN PCB 020 TPCUBR



Documents

Product Drawings

EP2.5 SHROUDED HDR ASSY 8P VERTICAL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1969730-8_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1969730-8_A.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1969730-8_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_1969730-8_1116201744_dmtec

English

MD_1969730-8_1116201744_dmtec

English

Agency Approvals

VDE Certificate

English