




Connectors > PCB Connectors > PCB Connector Accessories > Protection & Strain Relief > PCB Connector Covers



Protection & Strain Relief Accessory Type: **Cover**

Number of Positions: **34**

Centerline (Pitch): **2.54 mm [.1 in]**

Primary Product Material: **Thermoplastic**

Product Profile: **Low**

Features

Product Type Features

|                                           |                |
|-------------------------------------------|----------------|
| Protection & Strain Relief Accessory Type | Cover          |
| Product Profile                           | Low            |
| Connector Cover Type                      | Non-Polarizing |
| Sealable                                  | No             |

Configuration Features

|                     |    |
|---------------------|----|
| Number of Positions | 34 |
|---------------------|----|

Body Features

|                          |               |
|--------------------------|---------------|
| Connector Cover Side     | Front         |
| Primary Product Color    | Black         |
| Primary Product Material | Thermoplastic |

Housing Features

|                    |                |
|--------------------|----------------|
| Centerline (Pitch) | 2.54 mm[.1 in] |
|--------------------|----------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -65 – 105 °C[-85 – 221 °F] |
|-----------------------------|----------------------------|

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)




|                                               |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|-----------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                           |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                             |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2021 (211)<br>Candidate List Declared Against: JUN 2020 (209)<br>SVHC > Threshold:<br>1,6,7,8,9,14,15,16,17,17,18,18-dodecachloropentacyclo [12.2.1.16,9.02,13.05,10]octadeca-7,15-diene (Dechlorane Plus) (17% in Component Part)<br><b>Article Safe Usage Statements:</b><br>Wash thoroughly after handling. Do not handle until all safety precautions have been read and understood. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content                               | Not Low Halogen - contains Br or Cl > 900 ppm.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |
| Solder Process Capability                     | Not applicable for solder process capability                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



TE Part # 1-102394-5

34 AMP MODU MT HSG DR .100CL

Customers Also Bought




TE Part #1-338086-3  
RJ25 Connectors



TE Part #1534805-1  
HD20 COVER KIT 9POS WITH CABLE




TE Part #1-1658623-0  
50 NOVO MIL 30DP, LEAD FREE



TE Part #1-102536-5  
34 AMPMODU MT COVER DR .100CL




TE Part #1-1617150-6  
JMGSCD-5P = M39016/42-033P




TE Part #1-499374-0  
AMP-LATCH UNIVERSAL HEADERS




TE Part #YDTS20F21-39JNV001  
D38999: Square Flange, 21-39 insert



TE Part #1445693-2  
SOCKET CONTACT, QUADRAX, SZ8, RR



TE Part #102102-2  
MOD I RECP PLTD 30 SEL



TE Part #1-102541-8  
40 AMPMODU MT COVER DR .100CL

Documents

Product Drawings

34 AMPMODU MT COVER DR .100CL

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-102541-5\_N.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-102541-5\_N.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-102541-5\_N.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



AMPMODU\_INTERCONNECTION\_SYSTEM\_SECTION5\_CONT

English

Product Specifications

Application Specification

English