204131-1 ✔ ACTIVE


AMP

TE Internal #: 204131-1

Rack & Panel Covers & Plugs, Dust Cover, Receptacle, PVC, Cable-to-Panel, Sealable, Wire & Cable, Cable Mount (Free-Hanging)

View on TE.com >

Connectors > PCB Connectors > Backplane Connectors > Rack & Panel Backplane > Rack & Panel Covers & Plugs



Protection & Strain Relief Accessory Type: **Dust Cover**

Compatible With Connector Style: **Receptacle**

Primary Product Material: **PVC**

Connector System: **Cable-to-Panel**

Sealable: **Yes**

Features

Product Type Features

Protection & Strain Relief Accessory Type	Dust Cover
Connector System	Cable-to-Panel
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

Body Features

Primary Product Material	PVC

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)

Usage Conditions

Compatible With Connector Style	Receptacle
Operating Temperature Range	-65 – 125 °C[-85 – 257 °F]

Packaging Features

Packaging Method	Package

Other

Comment	For A404

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Customers Also Bought




TE Part #1057138-1
3004 7341 10




TE Part #YDTS26W23-35PEV001
D38999: Straight Plug, 23-35 Insert



TE Part #274133-000
0024A0024-3




TE Part #1-87962-4
30 MODII HORZ DR CE 100CL/115



TE Part #1-87962-8
38 MODII HORZ DR CE 100CL/115




TE Part #1532180-8
M83513/03-B12N, MCKS-N1-B-15P6Q9-36.0



TE Part #2-87962-8
58 MODII HORZ DR CE 100CL/115



TE Part #102263-000
55PC0811-2-9CS2502



TE Part #5-2176365-3
RQ 0603 140R 0.1% 10PPM 1K RL



TE Part #1-1589457-7
SSL025SC2DC012N = WDUALOBE

Documents

Product Drawings

DUST CAP, RECP, AD

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_204131-1_F.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_204131-1_F.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_204131-1_F.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages

ARINC 600 Next Generation Receptacle Connector

English