




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Tab**
Connector System: **Wire-to-Board**
Contact Mating Area Plating Material: **Gold**
Packaging Method: **Loose Piece**
Sealable: **No**

Features

Product Type Features

Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Contact Features

	15 µin
Wire Contact Termination Area Plating Material	Gold
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Phosphor Bronze
Contact Type	Tab
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	5 A

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Loose Piece



Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 583680-1
HSG AMP LEAF 15 POS



TE Part # 1-582355-5
RCPT AMP LEAF CRP POST 15 AU

Also in the Series | UTILUX CR



Board-to-Board Connector Contacts(4)



Card Edge Connector Housings(1)



Compression Connectors(7)



Insertion & Extraction Tools(1)



Wire-to-Board Connector Contacts(2)

Customers Also Bought




TE Part #5750340-1
Mini DIN, 8 pos, Vertical, Shield



TE Part #969047-3
MODU CRIMP CONTACT



TE Part #3669454001
MT5000-1/4-0-SP




TE Part #163618-1
CIS COSI PIN POST




TE Part #1991231-2
EMC CRIMP SLEEVE. IPT 16-50mms




TE Part #5-456403-2
CRIMPER, WIRE .062F PREMIUM



TE Part #6-215915-0
AMP-LATCH 15.2 HIGH TAPE



TE Part #6-216791-0
AMP LATCH D/P ASSY



TE Part #6-216792-4
AMP LATCH ASSY



TE Part #1991234-1
SHIELD BODY & WAVE SPRING ASSY

Documents



Product Drawings

RCPT AMP LEAF CRP POST 15 AU

English

Agency Approvals

Agency Approval Document

English

Agency Approval Document

English