



Connectors > Lighting Connectors > Plug & Socket Connector Accessories



Lighting Connector Accessory Type: **Tube**
Connector System: **Wire-to-Wire**
Number of Positions: **2**
Sealable: **No**
Connector & Contact Terminates To: **Wire & Cable**

Features

Product Type Features

Wire/Cable Type	SPT-2
Product Type	Accessory
Lighting Connector Accessory Type	Tube
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	2
---------------------	---

Electrical Characteristics

Voltage	42 VDC
Operating Voltage	125 VAC

Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Housing Features

Housing Color	White
---------------	-------

Operation/Application

Circuit Application	Power
---------------------	-------



Packaging Features

Packaging Method	Bag
------------------	-----

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



Also in the Series | NECTOR S



Insertion & Extraction Tools(3)

Lighting Cable Assemblies(1)

Plug & Socket Lighting Connector Accessories(57)

Plug & Socket Lighting Connectors(54)

Customers Also Bought

TE Part #2-292216-8
MINI CT D/R RELAY 28P V NAT

TE Part #293359-1
NECTOR S TUBE FOR SVT CABLE

TE Part #2-2071408-2
IHV100H5ANG

TE Part #293387-1
NECTOR S OUTLET HV-3 WHITE

TE Part #3-292216-0
MINI CT D/R RELAY 30P V NAT

TE Part #293388-3
NECTOR S PLUG HV-4 WHITE

TE Part #293388-2
NECTOR S PLUG HV-3 WHITE

TE Part #62922-1
250 FAST TAB AMVAR 032TPBR

TE Part #293388-1
NECTOR S PLUG HV-2 WHITE

TE Part #293390-1
MICRO QUADLOK SYSTEM SOCKET CONTACT

Documents

Product Drawings
NECTOR S TUBE FOR SPT2 CABLE

English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_293358-1_C_c-293358-1-c.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_293358-1_C_c-293358-1-c.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_293358-1_C_c-293358-1-c.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR_S_LINE_CONNECTOR_BROCHURE](#)

English

Agency Approvals

[UL Report](#)

English