




Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories



Flat Flexible Cable Accessory Type: Pull Tab

Features

Product Type Features

Flat Flexible Cable Accessory Type	Pull Tab
------------------------------------	----------

Body Features

Primary Product Material	Nylon
Primary Product Color	Black

Industry Standards

CSA File Number	LR 7189
Agency/Standard	CSA, UL
UL Rating	Recognized
UL File Number	E28476

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Comment	Receptacle Connector
---------	----------------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Not Yet Reviewed




Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Customers Also Bought




TE Part #867298-1  
6 POSITION RECEPTACLE KIT




TE Part #111446-1  
010 UNIV I/O 30DP NO EARS




TE Part #1532179-9  
M83513/03-A13N, MCKS-N1-B-9P6G1-72.0




TE Part #1803260-3  
CRIMPER, INSULATION F PREMIUM




TE Part #4-1803059-9  
ANVIL COMBINATION, END FEED




TE Part #448463-1  
LGH-1 RCPT,W/1/2-32 UN THREAD




TE Part #5-87631-7  
72 MODIV HSG COMP DR .100 POL



TE Part #533914-3  
HDI RECP ASSY 3 ROW 120 POS



TE Part #533935-1  
HDI PIN ASSY 4 ROW 100 POS



TE Part #ZPF000000000017895  
FAST-E 07 M-X-B 00 A

Documents

Product Drawings



50 A/L SNAP-ON PULL TAB

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-746601-1\_M.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-746601-1\_M.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1-746601-1\_M.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

English

Agency Approvals

Agency Approval Document

English