



Connectors > D-Shaped Connectors > D-Sub Accessories > D-Sub Covers



Connector Cover Type: Terminating

Number of Positions: 26

Operating Temperature Range: -55 – 105 °C [-67 – 221 °F]

Features

Product Type Features

Product Type	Accessory
Connector Cover Type	Terminating

Configuration Features

Number of Positions	26
---------------------	----

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



	Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 58430-1
TOOL, REPAIR

Also in the Series | AMPLIMITE 0.50 Series

			
D-Sub Backshells & Clamps(31)	D-Sub Covers(20)	D-Sub Locking & Mounting(8)	IDC D-Sub Connectors(77)



Insertion & Extraction Tools(1)



PCB D-Sub Connectors(196)

Customers Also Bought




TE Part #2-2064140-6
FOSM ODC LEAD 5.5 2PLUG-LC/PC



TE Part #5-87190-2
LOCKING CLIP CONT ASSY .025 SQ



TE Part #1-750877-5
50 50SR TERMINATOR COVER



TE Part #9-1437020-4
Female Socket Connectors: Strain Relief




TE Part #YDTS20Z15-15SNC001
D38999: Square Flange, 15-15 insert



TE Part #1803180-3
ANVIL, COMBINATION



TE Part #3-640432-7
07P MTA156 CONN ASSY 20AWG YEL



TE Part #216038-4
MOD-4 HSG+PULL TAB



TE Part #5-1377175-6
SMP 0-0160136-0



TE Part #5050094003
RNF-100-3/16-7-SP

Documents

Product Drawings

26 50SR TERMINATOR COVER

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1-750877-2_P.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1-750877-2_P.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-750877-2_P.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Customer Manual \(U.S.\)](#)

English