



MTA | MTA 100


TE Internal #: 3-644487-4

MTA 100, PCB Mount Header, Vertical, Wire-to-Board, 14 Position, 2.54mm [.1in] Centerline, 1 Row, Gold, Black Housing Color, Fully Shrouded

[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Headers & Receptacles >

Polyester Vertical PCB Header: 2.54mm, Shrouded, MTA 100



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **14**

Centerline (Pitch): **2.54 mm [.1 in]**

[All Polyester Vertical PCB Header: 2.54mm, Shrouded, MTA 100 \(57\)](#)

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	14
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------



Contact Features

Contact Layout	Inline
Contact Mating Area Length	5.1 mm[.2 in]
Mating Square Post Dimension	.64 mm[.025 in]
Contact Retention Within Housing	Without
PCB Contact Termination Area Plating Material Thickness	.76 µm[30 µin]
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Matte
Contact Shape & Form	Square
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Type	Pin
Contact Current Rating (Max)	5 A

Termination Features

Square Termination Post & Tail Dimension	.64 mm[.025 in]
Termination Post & Tail Length	3.56 mm[.14 in]
Termination Method to Wire & Cable	Solder
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Peg
Strain Relief	Without
Mating Alignment Type	Polarizing Tab
Mating Alignment	With
Panel Mount Feature	Without
PCB Mount Retention Type	Tab
Mating Retention Type	Friction Lock
PCB Mount Alignment	With
Mating Retention	With
PCB Mount Retention	With



Connector Mounting Type	Board Mount
-------------------------	-------------

Housing Features

Centerline (Pitch)	2.54 mm[.1 in]
Housing Color	Black
Housing Material	Polyester - GF

Dimensions

Connector Length	27.53 mm[1.084 in]
Connector Height	10.41 mm[.41 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Industry Standards

CSA Rating	Certified
UL Flammability Rating	UL 94V-0
Agency/Standard	CSA, UL
CSA File Number	LR7189
UL Rating	Recognized
UL File Number	E28476

Packaging Features

Packaging Quantity	500
Packaging Method	Package

Other

Comment	Straight post header style with polarized retention peg available upon request. Minimums may apply
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold



EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # CAT-104MTA-PLSCC Polyester PCB Connector Covers: 2.54 mm, MTA 100	 TE Part # CAT-104MTA-NYLCC Nylon PCB Connector Covers: 2.54 mm, MTA 100	 TE Part # CAT-104MTA-NGPNR Nylon Gold Plated Receptacle: 2.54 mm, No Mating Alignment, MTA 100	 TE Part # CAT-104MTA-NGPMR Nylon Gold Plated Receptacle: 2.54 mm, With Mating Alignment, MTA 100
--	---	---	---

Also in the Series | MTA 100

 Insertion & Extraction Tools(2)	 PCB Connector Covers(107)	 PCB Connector Keying(1)	 Standard Rectangular Connectors (1730)
--	---	--	---



Wire-to-Board Connector Contacts(18)



Wire-to-Board Headers & Receptacles (1182)

Customers Also Bought



TE Part #1-6609031-2
CORCOM R SERIES SINGLE PHASE FILTERS



TE Part #1-1623781-0
Wirewound Resistor: Vertical Mount



TE Part #1617155-2
MGAP-26W = MGA .100 GRID RELAY



TE Part #2-292174-5
CT Box Header SMT: Vert, Shrouded



TE Part #1-2215056-4
ASSY, EXTRACT TL, QSFP28 1X4




TE Part #2-2170747-1
CAGE ASSY, 1X4, QSFP28, SPRING, HS, LP



TE Part #91539-3
CCII TYPE II SKT 22-14 2x18 HEAD



TE Part #1-1618002-6
EV200H2ANA=RELAY, SPST-NO W /AUX



TE Part #1-1879808-9
RP 1J 511R 0.1% 15PPM 1K RL



TE Part #1-2176377-3
RQ 0805 178K 0.1% 10PPM 1K RL

Documents

Product Drawings

14P MTA100 SHRD HDR ASSY 30AU

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_3-644487-4_H.2d_dxf.zip

3-644487-4

MTA 100, PCB Mount Header, Vertical, Wire-to-Board, 14 Position, 2.54mm [.1in]
Centerline, 1 Row, Gold, Black Housing Color, Fully Shrouded



English

Customer View Model

[ENG_CVM_CVM_3-644487-4_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_3-644487-4_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[MTA, CST-100 II, SL-156 and AMP Economy Power \(EP\) Connectors](#)

English

Product Specifications

[Product Specification](#)

English

Agency Approvals

[CSA Certificate](#)

English