

MINI-MATCH

TE Internal #: 5164713-5
PCB Mount Header, Vertical, Board-to-Board, 5 Position, 2.5mm [.098in] Centerline, Unshrouded, Tin, Printed Circuit Board
[View on TE.com >](#)



Connectors > PCB Connectors > Board-to-Board Connectors > Board-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**
PCB Mount Orientation: **Vertical**
Connector System: **Board-to-Board**
Number of Positions: **5**
Centerline (Pitch): **2.5 mm [.098 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Board-to-Board
Header Type	Unshrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Rows	1
Number of Columns	5
PCB Mount Orientation	Vertical
Number of Positions	5

Contact Features

Contact Layout	Inline
Mating Tab Width	2.79 mm[.11 in]
Mating Tab Thickness	.5 mm[.02 in]
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	3.04 μm[120 μin]
Contact Type	Tab
Contact Current Rating (Max)	7 A



Termination Features

Rectangular Termination Post & Tail Thickness	.5 mm[.02 in]
Rectangular Termination Post & Tail Width	.78 mm[.03 in]
Termination Post & Tail Length	3.2 mm[.125 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

Mating Alignment	Without
PCB Mount Retention	Without
PCB Mount Alignment	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	2.5 mm[.098 in]
Housing Color	Green
Housing Material	PBT GF20

Dimensions

Connector Length	12.5 mm[.492 in]
Connector Height	5.9 mm[.232 in]
Connector Width	6.3 mm[.248 in]
PCB Thickness (Recommended)	1.6 mm[.06 in]

Usage Conditions

Operating Temperature Range	-40 – 85 °C[-40 – 185 °F][-40 – 185 °F]
-----------------------------	---

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Approved Standards	UL
UL Flammability Rating	UL 94V-0
Agency/Standard	UL
UL Rating	Recognized

Packaging Features

Packaging Quantity	3500
Packaging Method	Box



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2019 (201) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 240°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 5164711-5
05pos.MINI-MATCH FBTB, 2.5mm pitch







TE Part # 5164856-5
5 pos MINI-MATCH MALE ASS



TE Part # 5164897-5
05P MINI MATCH RA male, 2.5 mm pitch

Customers Also Bought



 TE Part #1-2273113-4 M12 MS-FS DOUBLE END CABLE ASSY BL	 TE Part #2176076-3 Metal Chip Resistor: Current Sense	 TE Part #1742803-1 FASTON 312 PCB TAB TPBR	 TE Part #1-1623746-3 ER74 1R0 5% AMMO PK
 TE Part #1676172-2 RN 0805 12K1 0.1% 10PPM 1KRL	 TE Part #1-284513-2 12 POS TERMI-BLOK HDR 900 POL.	 TE Part #1565749-3 SIGNAL HEADER	 TE Part #1879447-8 Wirewound Resistor: Mineral, 2.5 Kw
 TE Part #1-1879334-2 CPF 0603 2R61 1% 50PPM 1K RL	 TE Part #8-1415390-1 PE014H03		

Documents

Product Drawings

5P.MINI-MATCH ASSY

English

CAD Files

Customer View Model

ENG_CVM_5164713-5_A.3d_igs.zip

English

Customer View Model

ENG_CVM_5164713-5_A.3d_stp.zip

English

Customer View Model

ENG_CVM_5164713-5_A.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications



Mini Match Connection System

English

Product Specification

English

Product Specification

Instruction Sheets

Instruction Sheet (non U.S.)

German