




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Wire**

Number of Positions: **7**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	7
Number of Rows	1

Contact Features

Contact Layout	Inline
Contact Type	Socket
Contact Base Material	Brass

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------



Mechanical Attachment

Strain Relief	Without
Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Entry Configuration	Both Ends Closed
Housing Material	Nylon 66/6
Centerline (Pitch)	5 mm [.197 in]
Housing Color	Blue

Dimensions

Connector Length	9.2 mm [.362 in]
Connector Height	12.2 mm [.48 in]
Row-to-Row Spacing	5 mm [.197 in]

Usage Conditions

Operating Temperature Range	-40 – 110 °C [-40 – 230 °F]
-----------------------------	-----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed








China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 521208-1 POSI-LOK HSG.250-6 POS RAST5	 TE Part # 521206-1 POSI-LOK HSG.250-4 POS RAST5	 TE Part # 521207-1 POSI-LOK HSG.250-5 POS RAST5	 TE Part # 521207-3 HSG POSI-LOCK MARK III
 TE Part # 521207-4 HSG,RAST 5,POSI LOCK MKIII,5P	 TE Part # 521206-3 HSG,4P,POS LOCK,MKIII,250 SERI	 TE Part # 521206-6 POSI-LOK HSG.250-4 POS RAST5	 TE Part # 521208-4 HSG,250 POSI-LOCK,MKIII,6 POS,



TE Part # 521208-5
HSG,250 POSI-LOC,MKII,6P,NAT



TE Part # 521209-2
HSG POSI-LOCK MARK III



TE Part # 521206-2
250 SERIES 4 POS POSILOK HSG



TE Part # 521206-4
HSG,POSI-LOCK MKIII RAST,4P



TE Part # 521206-5
HSG,RECP,POSI-LOCK MKIII,4P



TE Part # 521207-2
POSI-LOK HSG 250 5P RAST5



TE Part # 521207-5
HSG POSI-LOK 250 (05-B) RAST



TE Part # 521208-2
HOUSING POSITIVE LOCK RAST



TE Part # 521208-6
HSG,POSI-LOCK MKIII RAST,6P



TE Part # 521835-4
HSG,RAST 5 PL,7P,BLOCK 3,5

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)



Connector Contacts(12)



Crimp Terminal Housings(41)



Insertion & Extraction Tools(1)



Rectangular Connector Housings(1)



Standard Edge Connectors(36)




Standard Rectangular Connectors(138)



Wire-to-Board Connector Assemblies
& Housings(214)



Wire-to-Board Connector Contacts(2)



Wire-to-Board Headers & Receptacles (424)

Customers Also Bought



TE Part #1-480705-0
06P UMNLCAP HSG NATL



TE Part #1-1879336-9
CPF 0603 357R 1% 50PPM 1K RL



TE Part #1062-20-0222
DEUTSCH STAMPED & FORMED CONTACTS



TE Part #YDTS24W17-99PAV001
Jam Nut: D38999, 17-99 Insert



TE Part #1452317-1
COVER F.16P JPT HSG



TE Part #1-794606-2
MICRO MNL RPT CNT STRP 30AU LF




TE Part #1217094-1
RCPT 250 POS-LOCK 18-14 0126BR



TE Part #1742539-3
CLUSTER BLOCK RECEPT,TPCuFeP



TE Part #103326-5
10 MODII HDR DRRA B/A .100CL



TE Part #172776-4
MIC MK-2 REC CONTACT LP

Documents

Product Drawings

POSI-LOK HSG.250-7 POS RAST5

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_521209-1_N.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_521209-1_N.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_521209-1_N.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[1654742_HOUSEHOLD_APPLIANCES_RAST5](#)

English

Agency Approvals

[UL Report](#)

English