



Connectors > D-Shaped Connectors > D-Sub Connector Contacts



Contact Type: **Pin**

D-Sub Contact Size: **8**

Contact Base Material: **Copper Alloy**

Contact Mating Area Plating Material: **Gold**

Termination Method to Wire & Cable: **Crimp**

Features

Product Type Features

Product Type	Contact
Connector & Contact Terminates To	Wire & Cable

Contact Features

	50 µin
Pin Diameter	.14 mm
Contact Style	Standard
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Gold
Contact Type	Pin
D-Sub Contact Size	8
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	32 A

Termination Features

Termination Post Length	.23 mm
Termination Method to Wire & Cable	Crimp

Dimensions

Post Diameter	.2 mm
Wire Size	8 mm²



Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

High Current	No
Circuit Application	Power

Packaging Features

Packaging Quantity	100
Packaging Method	Bag

Other

Comment	Use these contacts only with the Standard connectors. Do not use with Blindmate connectors.
---------	---

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Pb (4% in Contact/Component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 5532823-2
CONTACT, RECEPTACLE, POWER, RI

TE Part # 608651-1
HAND TOOL FRAME DANIELS

Customers Also Bought

TE Part #211161-1
SKT CONTACT ASSY

TE Part #1056443-1
2831 7388 02

TE Part #104257-6
07 MTE RCPT HSG SR LATCH .100

TE Part #1051650-1
2031 5005 00

TE Part #1051654-1
2031 5006 00 KIT, OSM STR PLUG

TE Part #1622766-1
LR2 1% 5K1

TE Part #YDTS26W09-35SNV001
D38999: Straight Plug, 09-35 Insert

TE Part #1056462-1
2837 7388 02

TE Part #1052071-1
2037 5007 00,SMA RA CABLE PLUG

TE Part #1052075-1
2037 5008 00,SMA RA CABLE PLUG

Documents

Product Drawings
PIN CONTACT ASSY
English



CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_211159-1_AM.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_211159-1_AM.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_211159-1_AM.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Product Specification

English

Instruction Sheets

Instruction Sheet (U.S.)

English

Agency Approvals

Agency Approval Document

English