



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Assemblies & Housings



Connector Product Type: **Housing**

Connector & Housing Type: **Receptacle**

Connector System: **Wire-to-Board**

Number of Positions: **2**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

Connector Product Type	Housing
Connector & Housing Type	Receptacle
Connector System	Wire-to-Board
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Keying & Polarized Rib Location	1a/2b
Number of Positions	2
Number of Rows	1

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Locking Latch Between Cavity Number	1&2
Strain Relief	Without



Panel Mount Feature	Without
PCB Mount Retention	Without
Mating Retention Type	Latch
Mating Retention	With
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Material	Nylon
Centerline (Pitch)	5 mm[.197 in]
Housing Color	Green

Dimensions

Connector Length	10 mm[.39 in]
Connector Height	14.4 mm[.567 in]

Usage Conditions

Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Industry Standards

RAST Version	02-E
Glow Wire Rating	Glow Wire
UL Flammability Rating	UL 94V-2

Packaging Features

Packaging Quantity	6000
Packaging Method	Bag

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211)



Does not contain REACH SVHC










Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
-----------------	--

Solder Process Capability	Not applicable for solder process capability
---------------------------	--


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 6-928247-2 2P ST-TIMER GEH	 TE Part # 928247-2 2P ST-TIMER GEH	 TE Part # 5-928247-3 STD TIMER GEH 3P	 TE Part # 4-928247-2 2P ST-TIMER GEH
 TE Part # 8-928247-2 STD TIMER GEH 2P	 TE Part # 9-928247-2 STD TIMER GEH 2P	 TE Part # 1-928247-1 11P ST-TIMER GEH	 TE Part # 3-1971845-2 2P, RAST 5 Tab Header, THV
 TE Part # 3-964951-2 STD TIMER GEH 2P	 TE Part # 2-928247-2 2P ST-TIMER GEH	 TE Part # 3-1971846-2 2P, RAST 5 Tab Header, THV	 TE Part # 3-928247-2 2P ST-TIMER GEH






TE Part # 5-928247-5
5P STD-TIMER GEH



TE Part # 6-928344-2
STD-TIMER GEH 2P



TE Part # 928247-6
6PST-TIMER HOUSING

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)



Connector Contacts(12)




Crimp Terminal Housings(41)




Insertion & Extraction Tools(1)



Rectangular Connector Housings(1)



Standard Edge Connectors(36)



Standard Rectangular Connectors(138)



Wire-to-Board Connector Assemblies & Housings(214)



Wire-to-Board Connector Contacts(2)




Wire-to-Board Headers & Receptacles (424)

Customers Also Bought



TE Part #60546-1
EXTRUDED RING CRIMP 18-14 AWG BR



TE Part #1969109-1
ULTRA-POD 250 ASSY REC 18-14 AWG BR



TE Part #1863025-1
UNIVERSAL MNL 6-WAY CAP



TE Part #1969206-1
ULTRA POD: Straight, Receptacle Assembly, Unplated, .250 inch



TE Part #521229-2
PL 250 HOUSING RECEPTACLE RED
NYLON 6/6

TE Part #1385725-3
.187 FLAG ULTRA POD

TE Part #5-1241961-8
3POS STD-TIMER HOUSING PITCH5
MK II

TE Part #521073-2
PLUG .125 HOUSING NYLON 66/6

TE Part #521163-2
POWER BLADE HSG 12P NYLON
BLACK

TE Part #794745-1
15P UMNL CAP HSG BLACK

Documents

Product Drawings

2P ST-TIMER GEH

English

2P ST-TIMER GEH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-928247-2_L.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-928247-2_L.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-928247-2_L.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

1654742_HOUSEHOLD_APPLIANCES_RAST5

English

Product Environmental Compliance

TE Material Declaration

English



Agency Approvals

VDE Certificate

English

VDE Certificate

English