




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Keying & Polarized Position Locations	1C, 2D, 3C, 4D
Number of Columns	4
PCB Mount Orientation	Vertical
Number of Positions	4
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features



Contact Layout	Inline
Contact Mating Area Length	8.5 mm[.33 in]
Contact Retention Within Housing	Without
PCB Contact Termination Area Plating Material Thickness	1 µm[39.37 µin]
Mating Tab Width	6.3 mm[.248 in]
Mating Tab Thickness	.8 mm[.032 in]
Contact Underplating Material Thickness	1.27 µm[50 µin]
PCB Contact Termination Area Plating Material Finish	Bright
Contact Shape & Form	Rectangle
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Silver
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Silver
Contact Mating Area Plating Material Finish	Bright
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]
Contact Type	Tab
Contact Current Rating (Max)	20 A

Termination Features

Square Termination Post & Tail Dimension	.8 mm[.032 in]
Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Polarizing Pegs
Mating Alignment Type	Keyed, Polarization
Mating Alignment	With
Mating Retention Type	Latch
PCB Mount Alignment	With
Mating Retention	With
PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	5 mm[.197 in]
--------------------	---------------



Housing Color	Natural
Housing Material	Nylon

Dimensions

Connector Length	22.6 mm[.88 in]
Connector Height	12.8 mm[.5 in]
Connector Width	14.9 mm[.58 in]
PCB Thickness (Recommended)	1.5 mm[.06 in]

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
Agency/Standard	UL
UL Rating	Recognized
UL File Number	E28476
VDE Tested	Yes

Packaging Features

Packaging Quantity	81
Packaging Method	Loose Piece, Tube/Box

Product Compliance

For compliance documentation, visit the product page on TE.com>








EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # 1-1971896-4 4P, RAST 5 Tab Header, THV	 TE Part # 1-2232046-4 4P, RAST 5 Tab Header, THV	 TE Part # 1971896-4 4P, RAST 5 Tab Header, THV	 TE Part # 2-2232046-4 4P, RAST 5 Tab Header, THV
 TE Part # 3-1971896-4 4P, RAST 5 Tab Header, THV	 TE Part # 3-2232046-4 4P, RAST 5 Tab Header, THV	 TE Part # 4-1971896-4 4P, RAST 5 Tab Header, THV	 TE Part # 4-2232046-4 4P, RAST 5 Tab Header, THV
 TE Part # 6-1971896-4 4P, RAST 5 Tab Header, THV	 TE Part # 7-1971896-4 4P, RAST 5 Tab Header, THV		

Also in the Series | RAST 5 IDC Connectors



Automotive Terminals(8)



Connector Contacts(12)




Crimp Terminal Housings(41)




Insertion & Extraction Tools(1)



Rectangular Connector Housings(1)



Standard Edge Connectors(36)



Standard Rectangular Connectors(138)



Wire-to-Board Connector Assemblies & Housings(214)




Wire-to-Board Connector Contacts(2)



Wire-to-Board Headers & Receptacles (424)

Customers Also Bought




TE Part #6-104074-4
22 SYSTEM 50 HDR SRRA SHRD SN



TE Part #1622943-1
CRG0603 1% 430K



TE Part #1622694-1
LR2 1% 16K




TE Part #2176317-5
MELF SMA-A 4R7 1% 50PPM 0207 1W



TE Part #1241171-3
MULTIFIT STE MK2 3P



TE Part #2-1445053-7
MICRO MNL HDR ASSY S/ROW LF



TE Part #104428-2
04 MODII HDR SRST B/A W/HD



TE Part #1375549-3
04 MTE VERT SMT HDR FULL SN-PB



Documents

Product Drawings

4P, RAST 5 Tab Header, THV

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-1971896-4_B_c-2-1971896-4-b.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-1971896-4_B_c-2-1971896-4-b.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-1971896-4_B_c-2-1971896-4-b.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

7-1773465-5 RAST5.0 Flyer

English

Product Specifications

Engineering Report

English

Agency Approvals

VDE Certificate

English