



Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Headers & Receptacles



PCB Connector Assembly Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **5**

Centerline (Pitch): **5 mm [.197 in]**

Features

Product Type Features

PCB Connector Assembly Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Fully Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Keying & Polarized Position Locations	2D
PCB Mount Orientation	Vertical
Number of Positions	5
Number of Rows	1

Electrical Characteristics

Operating Voltage	250 VAC
-------------------	---------

Contact Features

Contact Layout	Inline
----------------	--------



Contact Retention Within Housing	Without
PCB Contact Termination Area Plating Material Thickness	3.8 μm[149.606 μin]
Mating Tab Width	6.3 mm[.248 in]
Mating Tab Thickness	.8 mm[.032 in]
Contact Shape & Form	Square
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Base Material	Copper Alloy
Contact Mating Area Plating Material	Tin
Contact Mating Area Plating Material Finish	Matte
Contact Mating Area Plating Material Thickness	2 μm[.08 μin]
Contact Type	Tab
Contact Current Rating (Max)	16 A

Termination Features

Square Termination Post & Tail Dimension	.8 mm[.032 in]
Termination Post & Tail Length	3.5 mm[.138 in]
Termination Method to Wire & Cable	Solder
Termination Method to Printed Circuit Board	Through Hole - Solder

Mechanical Attachment

PCB Mount Alignment Type	Locating Posts
Mating Alignment Type	Keyed, Polarization
Mating Alignment	With
Mating Retention Type	Latch
PCB Mount Alignment	With
Mating Retention	With
PCB Mount Retention	Without
Connector Mounting Type	Board Mount

Housing Features

Centerline (Pitch)	5 mm[.197 in]
Housing Color	Natural
Housing Material	Nylon

Dimensions

--	--



Connector Length	12.8 mm[.5 in]
Connector Height	12.8 mm[.5 in]
PCB Thickness (Recommended)	1.5 mm[.06 in]
Row-to-Row Spacing	5 mm[.197 in]

Usage Conditions

Operating Temperature Range	-40 – 120 °C[-40 – 248 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Quantity	63
Packaging Method	Loose Piece, Tube/Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability





Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides




on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts


 TE Part # 2232043-5 5P, RAST 5 Tab Header, THV	 TE Part # 2232511-3 3P, RAST 5 TAB HEADER, THV	 TE Part # 2232512-5 5P, RAST 5 Tab Header, THV	 TE Part # 1971954-5 5P, RAST 5 Tab Header, THV
 TE Part # 2232045-2 2P, RAST 5 Tab Header, THV	 TE Part # 2232045-3 3P, RAST 5 Tab Header, THV	 TE Part # 2232045-6 6P, RAST 5 Tab Header, THV	 TE Part # 2232046-6 6P, RAST 5 Tab Header, THV
 TE Part # 2232511-6 6P, RAST 5 Tab Header, THV	 TE Part # 2232511-8 8P, RAST 5 Tab Header, THV	 TE Part # 2232511-4 3P, RAST 5 TAB HEADER, THV	

Also in the Series | RAST 5 IDC Connectors

 Automotive Terminals(8)	 Connector Contacts(12)	 Crimp Terminal Housings(41)	 Insertion & Extraction Tools(1)
--	--	--	--



Rectangular Connector Housings(1)



Standard Edge Connectors(36)




Standard Rectangular Connectors(138)



Wire-to-Board Connector Assemblies & Housings(214)



Wire-to-Board Connector Contacts(2)



Wire-to-Board Headers & Receptacles (424)


Customers Also Bought



TE Part #1744525-3
EP 03P RA-HDR ASY NO 2 PIN



TE Part #2232957-1
250 POSITIVE REC EX MK-2



TE Part #280081-1
FF 250 TAB 18-13 AWG BR




TE Part #1-2232979-3
SGI2.0 PLUG ASSEMBLY 3P,KEY A



TE Part #160824-6
FF 250 REC 0.5-2.5MM2 PB



TE Part #171370-6
CLUSTER BLOCK HSG 66 0023



TE Part #2178453-1
.090 CLUSTER REC.



TE Part #2232511-7
7P, RAST 5 TAB HEADER, THV



TE Part #284932-8
DUOPLUG STD FEMALE CONN., 8 POS.



TE Part #917688-6
SIGNAL DOUBLE LOCK PLUG HSG 4P BLUE

Documents



Product Drawings

3P, RAST 5 TAB HEADER, THV

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2232511-5_A_c-2232511-5-a.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2232511-5_A_c-2232511-5-a.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2232511-5_A_c-2232511-5-a.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Engineering Report

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English

UL Report

English