



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Connector Accessories



Flat Flexible Cable Accessory Type: **Mounting Bolt**

Features

Product Type Features

Flat Flexible Cable Accessory Type	Mounting Bolt
------------------------------------	---------------

Body Features

Primary Product Material	Stainless Steel
--------------------------	-----------------

Dimensions

Product Length	11.05 mm[.435 in]
----------------	-------------------

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Other

Comment	2-56 bolts and nuts may be used to mount pin headers with and without latches. If latches are to be used, the bolts must be positioned in the pin header before the latches are installed.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant



China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer


This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 102198-1
A/L HARDWARE FOR EJECTION KIT

Also in the Series | AMP-LATCH Universal Headers




Ribbon Cable Connectors(525)




Ribbon Connector Accessories(14)

Customers Also Bought







TE Part #102156-6
AMP-LATCH UNIVERSAL HEADERS




TE Part #102198-1
A/L HARDWARE FOR EJECTION KIT




TE Part #1-1617037-3
HFW5A1201L00 = HFW5A RELAY




TE Part #1053256-1
2058 5305 00




TE Part #146130-1
04 MODII HDR DRST SFMNT B/A




TE Part #1-1617084-3
SRAW-4C-24B = HALF.4 POLE.24V.




TE Part #YHDP26-24-7SN-CL22
DEUTSCH HDP20 HOUSINGS



TE Part #1218125-1
AMPLIMITE,ASY,PLUG,LOW PROF, 109,1



TE Part #104483-1
08 SHORT PT RCPT HSG DR .100CL



TE Part #1050934-1
2002 8207 92

Documents

Product Drawings

A/L MT SCREW

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_746383-1_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_746383-1_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_746383-1_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



AMPMODU_INTERCONNECTION_SYSTEM_SECTION5

English

Ribbon Cable Interconnect Solutions

English

Agency Approvals

Agency Approval Document

English