



Connectors > PCB Connectors > PCB Connector Accessories > PCB Connector Hardware > PCB Latches, Locks & Retainers



Connector & Contact Retention Accessory Type: **Snap Latches**

Connector & Contact Terminates To: **Printed Circuit Board**

Operating Temperature Range: **-40 – 70 °C [-40 – 158 °F]**

Features

Product Type Features

Connector & Contact Retention Accessory Type	Snap Latches
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

Number of Columns	5
-------------------	---

Mechanical Attachment

Hardware Material	Brass, Copper Alloy
-------------------	---------------------

Usage Conditions

Operating Temperature Range	-40 – 70 °C[-40 – 158 °F]
-----------------------------	---------------------------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
------------------	-------------------------------

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Product Compliance



For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Also in the Series | Z-PACK 2mm HM

Backplane Coding Keys(60)

Backplane Connector Housings(4)

Backplane Guide Hardware(37)

Backplane Power Connectors(7)

Board-to-Board Connector Contacts(5)

Hard Metric Backplane Connectors (272)

Insertion & Extraction Tools(2)


PCB Connector Covers(4)



PCB Connector Shrouds(39)



PCB Ferrules & Shields(19)




PCB Latches, Locks & Retainers(1)



Rectangular Power Connectors(87)


Customers Also Bought




TE Part #3-826199-0
GUIDE BRACKET



TE Part #1-84533-3
1.25mm FPC Connectors



TE Part #1445999-2
AMP Power 120A Con KIT,4 AWG, BLUE




TE Part #1-966066-9
TUBULAR END-FERRULE




TE Part #1734580-1
MOD-Jack,RJ45, 8P8C, SHD LP, 6u" Au



TE Part #2102515-2
Fortis Zd 2PR EMI Assy RA 93/7 SnPb Tail



TE Part #5223172-1
2MM FB,ASY,008,PWR,HDR,EN,4.25



TE Part #1-1879619-3
H8 33R 1% 25PPM



TE Part #1393115-7
KUIP-11D15-24=KU



TE Part #9-1437514-3
322-HCS5P3-100LF=LF HOLTITE

Documents

Product Drawings

ZP,LATCH 10MM LIFSH

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_352706-1_B.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_352706-1_B.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_352706-1_B.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

TE Material Declaration

English