



Connectors > D-Shaped Connectors > D-Sub Connectors > Box Mount D-Sub Connectors



Connector & Housing Type: **Receptacle**
Connector System: **Cable-to-Cable**
Number of Positions: **36**
Power/Signal/Coax Combination: **Yes**
D-Sub Shell Size: **5**

Features

Product Type Features

Product Type	Connector
Connector & Housing Type	Receptacle
Connector System	Cable-to-Cable
D-Sub Shell Size	5
Sealable	No
Blindmate	No

Configuration Features

Number of Positions	36
Power/Signal/Coax Combination	Yes

Body Features

Box Mount D-Sub Connector Insert Arrangement	36C4
Retention Clip Material	Stainless Steel
Shell Plating Material	Zinc
Shell Material	Steel
Non-Magnetic	No

Contact Features

Contact Type	Socket
D-Sub Contact Size	20, 8



Contact Current Rating (Max)	7.5 A, 32 A
------------------------------	-------------

Mechanical Attachment

Mounting Hole Diameter	3.05 mm[.12 in]
------------------------	-----------------

Housing Features

Centerline (Pitch)	2.77 mm[.109 in]
--------------------	------------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

ULTRA-LITE Connector	No
Circuit Application	Power & Signal

Industry Standards

NASA Qualification	No
--------------------	----

Packaging Features

Packaging Method	Package
------------------	---------

Other

Comment	Cable clamp/strain relief hardware cannot be used with these arrangements.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2019 (197) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Wave solder capable to 265°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent




chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 318813-1
EXTRACTION TOOL ASSY

Customers Also Bought



TE Part #1617037-9
HFW5A1201K00 = HFW 5AMP RELAY




TE Part #1410946-1
MULTI-GIG SOC. CAP SCREW, CUSTOMIZED HDW



TE Part #1-1469492-8
MULTIGIG RT 9MM GUIDE/ESD 315 DEG




TE Part #1-1469492-9
MULTIGIG RT 9MM GUIDE/ESD UNKE



TE Part #1060498-1
5182 2240 00



TE Part #1419111-6
24A110=TRACK,MOUNTING



TE Part #1-520532-3
8 SDL RND PLUG ASSY 36 SERIES



TE Part #1052071-1
2037 5007 00,SMA RA CABLE PLUG



TE Part #1-2000713-3
RA Keyed Guide Mod, Vita 46, Machined



TE Part #ZPF000000000147876
M39029/5-115

Documents



Product Drawings

AMPLIMITE RECEPT ASY,COAX MIX

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-208550-1_AF.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-208550-1_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-208550-1_AF.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Agency Approvals

UL Report

English