



Terminals & Splices > Splices



Splice Product Type: **Splice**
Terminal & Splice Type: **Splice**
Wire Size: **.61 – 1.21 mm²**
Sealable: **Yes**

Features

Product Type Features

Splice Product Type	Splice
Sealable	Yes
Splice Type	In-Line Splice
Serrated	No
Splice Accessory Type	Splice
Splice Barrel Type	Closed Barrel
Splice Wire/Cable Type	Insulated Wire
Insulated	Yes
Support Style	Non-Insulation Support

Configuration Features

Number of Serrations	0
----------------------	---

Body Features

Insulation Material	Modified Polyvinylidene
Splice Features	Splice Kit
Splice Material	Nickel-Plated

Contact Features

Terminal & Splice Type	Splice
------------------------	--------

Dimensions

Wire Size	1216 – 2426 CMA
-----------	-----------------



Barrel Inside Diameter	1.69 mm[.067 in]
Splice Overall Length	29.21 mm[1.15 in]

Usage Conditions

Insulation Requirement	Fully Insulated
Operating Temperature Range	-55 – 175 °C[-67 – 347 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	Yes
-----------------------------	-----

Packaging Features

Splice Packaging Method	Bag/Box
-------------------------	---------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 1752939-1
SDE DIE-26-12 MINI SEAL SPLICE

TE Part # 992008-000
AD-1377-CRIMP-TOOL-3-CVTY

Customers Also Bought

TE Part #1577621-1
TERMINAL RT PIDG PEEK STRATO 24-22 AWG

TE Part #280095-2
FF 250 REC 0.3-0.8MM2 PTBR

TE Part #2-320093-1
TERMINAL,SOLIS R 16-14 10

TE Part #218448-001
22759/41-20-9

TE Part #2560-215-1631L
CONT PIN

TE Part #ZPF000000000122870
951-06 R 18-800 S 50-090

TE Part #216787-000
SO96-3-55-22-90

TE Part #1577637-1
TERMINAL RT PIDG PEEK STRATO 14-12 AWG

TE Part #217595-000
22759/42-20-9

TE Part #2180793001
55A0811-22-0

Documents

Product Drawings

D-436-83

English

Datasheets & Catalog Pages

1654025_Sec8_D-436

English



[Harness Repair Products Quick Reference Guide](#)

English