




Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Spade Tongue**

Wire Size: **509 – 3260 CMA**

Ring & Spade Stud Size: **#4**

Features

Product Type Features

Shape Description	SPADE-047
Ring & Spade Stud Size	#4
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Terminal Angle	Straight
----------------	----------

Body Features

Inspection Slot	No
Ring & Spade Plating Material	Tin

Contact Features

Terminal & Splice Type	Spade Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment



Wire Insulation Support	Without
-------------------------	---------

Dimensions

Wire Size	509 – 3260 CMA
Stud Diameter	2.8 mm[.112 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	14.1 mm[.555 in]
Barrel Inside Diameter	1.55 mm[.061 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	170 °C[338 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer




This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 525693
DAHT SOLIS 22-10 ASSY

Customers Also Bought

			
TE Part #1577639-1 TERMINAL RT PIDG PEEK STRATO 14-12 AWG	TE Part #1577620-1 TERMINAL RT PIDG PEEK STRATO 24-22 AWG	TE Part #1577621-1 TERMINAL RT PIDG PEEK STRATO 24-22 AWG	TE Part #151438 PIDG 22 RING #4
			
TE Part #142841-1 TUBING SPIRAP 500031-1	TE Part #1577632-1 TERMINAL RT PIDG PEEK STRATO 18-16 AWG	TE Part #1577633-1 TERMINAL RT PIDG PEEK STRATO 18-16 AWG	TE Part #1377172-4 SMP 0-0130017-0



Documents

Product Drawings

BRAZED 22-16 SPADE #4

English

Product Environmental Compliance

TE Material Declaration

English

Agency Approvals

UL Report

English