




Connectors > D-Shaped Connectors > D-Sub Connector Contacts > D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20



Contact Type: **Socket**
D-Sub Contact Size: **20**
Contact Base Material: **Phosphor Bronze**
Contact Mating Area Plating Material: **Gold**
Termination Method to Wire & Cable: **Solder**

[All D-Sub Conn Contacts: Socket, Phosphor Bronze, Signal, Size 20 \(58\)](#)

Features

Product Type Features

Product Type	Contact
Grade	Standard
Connector System	Cable-to-Cable
Connector & Contact Terminates To	Wire & Cable

Contact Features

	30 μin
Pin Diameter	1.02 mm
Contact Underplating Material	Nickel
PCB Contact Termination Area Plating Material	Tin
Contact Type	Socket
D-Sub Contact Size	20
Contact Base Material	Phosphor Bronze
Contact Mating Area Plating Material	Gold



Contact Current Rating (Max)	3.1 A
------------------------------	-------

Termination Features

	.37 in
Termination Method to Wire & Cable	Solder

Mechanical Attachment

Contact Retention Type Within Housing	Snap-In
Wire Insulation Support	Without

Dimensions

Post Diameter	2.16 mm
Wire Size	.8 – .9 mm ²

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Packaging Features

Packaging Quantity	10000
Packaging Method	Loose Piece

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer



This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 91285-1


INSERT/EXTRACT TOOL ASSEMBLY

Customers Also Bought



TE Part #205203-8

D-Sub Crimp Recpt Signal 9 Posn, Socket Size 20, Shell Size 1




TE Part #2-2822979-4

LGA 3647 SOCKETS



TE Part #1-206062-4

CPC CABLE CLAMPS



TE Part #2-2330551-2

SOCKET P4/P5 BACKPLATE ASSY, STUD 7.12MM



TE Part #1825256-3

MHS133RA04=SP3T SL SW R/A AG




TE Part #1052092-1

2037 5056 00





TE Part #1052421-1

2052 0000 00,SMA FM JACK RECPT



TE Part #1057381-1

3082 2241 00



Documents

Product Drawings

20DF SOCKET CONT. L.P.

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_66569-3_AD_c-66569-3-ad.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_66569-3_AD_c-66569-3-ad.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_66569-3_AD_c-66569-3-ad.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Signal Contacts

English

AMPLIMITE Subminiature D Connectors - Cable Connectors

English

AMP Circular Connectors for Commercial Signal & Power Applications

English

AMPLIMITE Cable Connectors and Shielding Hardware Kits QRG

English

Product Specifications

Application Specification

English

Product Environmental Compliance

MD_66569-3_07192018726_dmtec

English

MD_66569-3_07192018726_dmtec



English

Instruction Sheets

Instruction Sheet (U.S.)

English