



Terminals & Splices > Splices

Splice Product Type: **Splice**Terminal & Splice Type: **Splice**Wire Size: **.15 – .61 mm²**Barrel Inside Diameter: **1.2 mm [.048 in]**

Features

Product Type Features

Splice Product Type	Splice
Splice Type	In-Line Splice
Serrated	No
Splice Accessory Type	Splice
Splice Barrel Type	Closed Barrel
Splice Wire/Cable Type	Insulated Wire
Insulated	No
Support Style	Non-Insulation Support

Configuration Features

Number of Serrations	0
----------------------	---

Body Features

Splice Material	Tin-Plated Copper
-----------------	-------------------

Contact Features

Terminal & Splice Type	Splice
------------------------	--------

Dimensions

Wire Size	304 – 1216 CMA
Barrel Inside Diameter	1.2 mm[.048 in]
Splice Overall Length	12.95 mm[.51 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified Splice	No
-----------------------------	----

Packaging Features

Splice Packaging Method	Bag/Box
-------------------------	---------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Out of Scope - excluded from Halogen requirements
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 992008-000
AD-1377-CRIMP-TOOL-3-CVTY


Customers Also Bought



TE Part #2-320569-5
PIDG RING TONGUE TERMINALS



TE Part #0660-206-1282
CONT PIN




TE Part #211137-000
CTA-0161



TE Part #YDTS26W25-61PNV001
D38999: Straight Plug, 25-61 Insert



TE Part #1-1604800-4
ASSY,PLUG,QUADRAX,FREE
HANGING,12 POS



TE Part #1445693-4
BACC47GB1 - SCKT CONTACT,
QUADRAX,SZ8,RR



TE Part #253627-000
MTCP-122-20S2



TE Part #226335-000
CTA-0166



TE Part #1616055-3
A1077DD (FAA/PMA)=CONTACTOR -
S.P.S.T.



TE Part #237171-000
MTC100-JH2-P32

Documents

Product Drawings

[D-609-06](#)

English

Datasheets & Catalog Pages

[1654025_Sec8_D-436](#)

English

Raychem Electrical Interconnect Products

English

680326-000

Splices, Splice, Splice, 26 – 20AWG Wire Size, .15 – .61mm² Wire Size, Barrel Inside
Diameter .048 in [1.2 mm], 304 – 1216CMA Wire Size

