



AMP | AMP Type II

TE Internal #: 201328-1

AMP Type II, Power Contacts, Contact, Gold, 24 – 20AWG Wire Size, .2 – .6mm² Wire Size, Wire-to-Wire, 1 Position, Wire & Cable, Crimp

[View on TE.com >](#)

Connectors > Power Connectors > Power Contacts



Power Contact Type: **Contact**
Contact Mating Area Plating Material: **Gold**
Wire Size: **.2 – .6 mm²**
Connector System: **Wire-to-Wire**

Features

Product Type Features

Power Contact Type	Contact
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	1
---------------------	---

Electrical Characteristics

Test Current	13 A
--------------	------

Contact Features

Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	13 A
Contact Type	Socket
Contact Retention Within Housing	With
Mating Pin Diameter	1.57 mm[.062 in]
Contact Base Material	Brass
Contact Mating Area Plating Material Thickness	.76 µm[30 µin]
Contact Mating Area Plating Material Finish	Bright
Wire Contact Termination Area Plating Material Thickness	.76 µm[30 µin]
Wire Contact Termination Area Plating Material	Gold



Contact Orientation	Straight
Contact Underplating Material	Nickel
Contact Underplating Material Thickness	1.27 µm[50 µin]
Contact Size	16

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Contact Retention Type Within Housing	Snap-In
Wire Insulation Support	With

Dimensions

Wire Size	.2 – .6 mm²
Accepts Wire Insulation Diameter Range	1.4 – 2.24 mm[.055 – .088 in]

Usage Conditions

Operating Temperature Range	-55 – 105 °C[-55 – 302 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Identification Marking

Color Code	Yellow/Red
------------	------------

Packaging Features

Packaging Method	Bag
Packaging Quantity	1000

Other

Wire/Cable Type	Discrete Wire
For Use With	CPC Series 1 and 4 Connectors, G Series Connectors, M Series Connectors, Metrimate Drawer, Metrimate, Special M Series
Comment	Extraction Tool No. 305183, Insertion Tool No. 200893-2 (for insulation diameters 1.78 [0.07] or less), Use turret TH501 (p/n 1-601967-5) with hand tool 601967-1.

Product Compliance

For compliance documentation, visit the product page on TE.com>



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	BFR/CFR/PVC Free, but Br/Cl >900 ppm in other sources.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # CAT-AM71-C83998C
CMC SERIES 1

TE Part # CAT-AM71-C83998Y
CPC SERIES 1 SEALED ONE-PIECE

TE Part # CAT-AM71-C83998J
CPC SERIES 1

TE Part # CAT-AM71-C83998K
CPC SERIES 6

TE Part # 200893-2
INSERTION TOOL CONT



TE Part # 539972-1
EXTRACTION TOOL

TE Part # 305183
EXTRACT TOOL TYPE 2 20-16

TE Part # 601967-1
CRIMPING TOOL M22520/1-01




Also in the Series | AMP Type II



Customers Also Bought





Documents

Product Drawings

CONTACT SOCKET ASSY.

English

CAD Files

Customer View Model

ENG_CVM_201328-1_AF.3d_igs.zip

English

Customer View Model

ENG_CVM_201328-1_AF.3d_stp.zip

English

Customer View Model

ENG_CVM_201328-1_AF.2d_dxf.zip

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Signal Contacts

English

M_SERIES_PIN_AND_SOCKET_CONNECTORS

English

AMP Circular Connectors for Commercial Signal & Power Applications

English

Product Specifications

Application Specification

English

Type II Screw Machine Contacts

Japanese

Application Specification

Japanese

Application Specification

Japanese



Product Environmental Compliance
TE Material Declaration

English

Instruction Sheets
Instruction Sheet (U.S.)

English

Application and Maintenance for Crimping Die Assemblies
English

Instruction Sheet (U.S.)
English

Instruction Sheet (U.S.)
English

Instruction Sheet (U.S.)
English

Instruction Sheet (U.S.)
Japanese