




Connectors > Lighting Connectors > LED Holders



Compatible LED: Lumileds LUXEON CoB 1202, Lumileds LUXEON CoB 1203

Lighting Connector Features Included: Does Not Enable Zhaga Compatibility, Not Optic Compatible

Operating Voltage: 100 VDC

Termination Method to Wire & Cable: Poke-In

Connector & Contact Terminates To: Wire & Cable

Features

Product Type Features

Product Type	LED Holder
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Lighting Connector Features Included	Does Not Enable Zhaga Compatibility, Not Optic Compatible
--------------------------------------	---

Electrical Characteristics

Current Rating (Max)	1 A
Operating Voltage	100 VDC

Body Features

Compatible LED	Lumileds LUXEON CoB 1202, Lumileds LUXEON CoB 1203
----------------	--

Contact Features

Contact Mating Area Plating Material	Gold
Contact Base Material	Copper Alloy

Termination Features

Termination Method to Wire & Cable	Poke-In
------------------------------------	---------

Mechanical Attachment

Connector Mounting Type	Board Mount
-------------------------	-------------



Housing Features

Housing Material	LCP (Liquid Crystal Polymer)
------------------	------------------------------

Usage Conditions

Operating Temperature Range	-25 – 105 °C[-13 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





TE Part # CAT-B8519-P7565
BUCHANAN WIREMATE POKE-IN




TE Part # 2324697-2
PUSH GRIP CONNECTOR 2P



TE Part # 2-2834245-1
2P, FLEX GRIP WIRE CONNECTOR

Also in the Series | LUMAWISE LED Holders



LED Holders(79)

Customers Also Bought



TE Part #2325811-3
Z45 LED HOLDERS



TE Part #2-2314846-0
20P,2MM,BB,REC,DRV,T,SMD,AU.76, TB,W/CP



TE Part #5-1879351-0
RR01 5% 330K AMMO



TE Part #5-1879351-5
RR01 5% 510K AMMO



TE Part #2337228-1
TACT ULTRA JB 3.0X2.6X0.65 100GF



TE Part #5-1419111-5
PT271110



TE Part #2-1827391-1
Glow Wire GRACE INERTIA Header



TE Part #770091-1
09P .093 COMM P&S RECPT HSG



TE Part #ZPF000000000007412
983-0S 18-31 SN



TE Part #7-2176373-7
RQ 0805 61R9 0.1% 10PPM 1K RL



Documents

Product Drawings

LUMAWISE LED HOLDER, TYPE LUMIPACK N1

Japanese

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2134318-1_C.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2134318-1_C.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2134318-1_C.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Specifications

Application Specification

Japanese

Product Environmental Compliance

Product Compliance

English

Product Compliance

English

Agency Approvals

Agency Approval Document

English