



Terminals & Splices > Ring Terminals & Spade Terminals



Terminal & Splice Type: **Ring Tongue**

Wire Size: **202 – 810 CMA**

Ring & Spade Stud Size: **#2, M2**

Features

Product Type Features

Shape Description	RING-049
Ring & Spade Stud Size	#2, M2
Ring & Spade Barrel Type	Closed Barrel
Sealable	No
Insulated	No
Ring & Spade Wire/Cable Type	Regular Wire
Support Style	Non - Insulation Support

Configuration Features

Number of Holes	1
Terminal Angle	Straight

Body Features

Inspection Slot	No
Weight per Piece	.136 g
Ring & Spade Plating Material	Copper, Nickel

Contact Features

Terminal & Splice Type	Ring Tongue
Ring & Spade Terminal Orientation	Straight

Mechanical Attachment

Wire Insulation Support	Without
-------------------------	---------



Dimensions

Wire Size	202 – 810 CMA
Stud Diameter	2.36 mm[.093 in]
Tongue Thickness	.79 mm[.031 in]
Ring & Spade Overall Length	8.36 mm[.329 in]
Barrel Inside Diameter	.89 mm[.035 in]

Usage Conditions

Insulation Requirement	Uninsulated
Operating Temperature Range	343 °C[649 °F]

Operation/Application

Heavy Duty	No
------------	----

Industry Standards

Government Qualified	No
----------------------	----

Packaging Features

Packaging Quantity	1000
Ring & Spade Packaging Method	Loose Piece

Other

Line	Budget
------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUN 2020 (209) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 69363
DAHT STRATO SOLIS 26-20 ASSY



TE Part # 2217483-2
KIT, BTLI, DOUBLE ACTION HEAD



TE Part # 2217483-1
KIT, BTLI, DOUBLE ACTION HEAD

Also in the Series | SOLISTRAND Budget



Knife Disconnects(4)




Ring Terminals & Spade Terminals(181)



Splices(1)

Customers Also Bought



TE Part #2-1625984-5
Power Resistors: Aluminum Housed, HSA



TE Part #1-1757820-0
AMPLIMITE,ASY,RCPT,STD,109,ZN,5,CT



TE Part #1-1757819-0
AMPLIMITE,ASY,PLUG,STD,109,ZN,5,CT



TE Part #1532204-1
M83513/02-DN, MCKS-N1-B-25SS



TE Part #1532213-1
M83513/01-EN, MCKS-N1-B-31PS

TE Part #2-322796-1
STRATO R 22-16COMM 22-18MIL 4

TE Part #SP1-12
CABLE ACTUATED POSITION STOCK LIST

TE Part #1-647402-2
3.96mm Wire-to-board housing: receptacle, with mating alignment, SL 156

TE Part #1-51864-0
PIDG RING TONGUE TERMINALS

Documents

Product Drawings

TERM,BUDG R 26-22 2 NIPL

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_2-31425-3_V.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2-31425-3_V.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_2-31425-3_V.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

Product Compliance

English

Product Compliance

English